# **Product datasheet**

Specifications





# TeSys GS - switch-disconnector fuse - 3 P - 160 A - DIN 0

GS1LD3

#### Main

TeSys
TeSys GS
GS1 L
Switch-disconnector-fuse
Protection
3P
3t
3 NO
160 A (at 40 °C)
125 A at 440 V 2 poles in series per phase DC-23A 125 A at 440 V 2 poles in series per phase DC-23B 125 A at 690 V with terminal cover AC-23A 125 A at 690 V with terminal cover AC-23B 160 A at 400 V AC-23A 160 A at 400 V AC-23B 160 A at 500 V AC-23A 160 A at 500 V AC-23B
DIN
0
AC DC
50/60 Hz

### Complementary

Type Of Operating Handle	Direct right side
Mounting Support	Plate
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 KV
Rated Operational Power In W	90 kW at 400 V 110 kW at 500 V 110 kW at 690 V
Breaking Capacity	15 W
Making Capacity	1600 A at 400 V AC-23B
Breaking Capacity	1280 A at 400 V (AC-23B)
Short-Circuit Withstand	20 kA
Mechanical Durability	10000 cycles

Electrical Durability	1000 cycles AC-23A 1000 cycles AC-23B 200 cycles DC-23A 200 cycles DC-23B
Connections - Terminals	Power circuit: bars Power circuit: lugs-ring terminals5095 mm² flexible
[Icm] Rated Short-Circuit Making Capacity	100 kA at 400 V with protection by gG fuses
Tightening Torque	Power circuit: 12 N.m - on bars Power circuit: 12 N.m - on lugs-ring terminals

#### Environment

Standards	IEC 60947-3
Product Certifications	CE
Protective Treatment	тн
Ip Degree Of Protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient Air Temperature For Operation	-2070 °C
Ambient Air Temperature For Storage	-4080 °C
Fire Resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	162 mm
Width	192 mm
Depth	136.5 mm
Net Weight	1.8 kg

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	17 cm
Package 1 Length	26.4 cm
Package 1 Weight	2.205 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	24
Package 2 Height	75 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	62.944 kg

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information