# **Product datasheet**

Specification





# Motor circuit breaker, TeSys GV5, 3P, 220A, Icu 70kA, thermal magnetic

GV5P220H

#### Main

Range Of Product	TeSys GV5
Range	TeSys
Device Short Name	GV5P
Product Name	TeSys GV5 TeSys Giga
Product Or Component Type	Motor circuit breaker
Device Application	Motor protection
Trip Unit Technology	Electronic

### Complementary

•	
Poles Description	3P
Utilisation Category	Category A conforming to IEC 60947-2
Motor Power Kw	90110 kW at 400/415 V AC 50/60 Hz 110 kW at 500 V AC 50/60 Hz 110132 kW at 660/690 V AC 50/60 Hz
Breaking Capacity	70 kA Icu at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Control Type	Direct rotary handle
[In] Rated Current	220 A at 65 °C
Magnetic Tripping Current	3300 A
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Ith] Conventional Free Air Thermal Current	220 A conforming to IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	8 kV
Power Dissipation Per Pole	17.6 W
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles for AC-3 at 400/415 V In
Maximum Operating Rate	25 cyc/h
Rated Duty	Continuous
Connection Pitch	35 mm without spreaders

Connections - Terminals	Bars Lugs	
Tightening Torque	15 N.m M8 screw type	
Mechanical Robustness	Vibrations: +/- 1 mm 213.2 Hz conforming to IEC 60068-2-6 Vibrations: 0.7 gn 13.2100 Hz conforming to IEC 60068-2-6	
Phase Failure Sensitivity	Yes conforming to IEC 60947-4-1	
Height	161 mm	
Width	105 mm	
Depth	155 mm	
Net Weight	2.6 kg	
Colour	Anthracite (RAL 7016)	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	

#### **Environment**

Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	IECEE CB Scheme EAC (pending)
Climatic Withstand	conforming to IACS E10
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ambient Air Temperature For Storage	-5085 °C
Fire Resistance	960 °C conforming to IEC 60695-2-11
Operating Altitude	5000 m
Ambient Air Temperature For Operation	-2570 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.1 cm
Package 1 Width	11.8 cm
Package 1 Length	17.0 cm
Package 1 Weight	2.9 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	18.1 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information