
Product datasheet





Straight length, Canalis KTA, aluminium, 3200A, 3L+N+PE, high Icw, fixed length 2m, 1 outlet for bolt on tap off unit

KTA3200EB620

Main

Range	Canalis	
Product Name	КТ	
Product Or Component Type	Busbar trunking	
Busbar Description	Distribution length	
Device Short Name	КТА	
Tap-Off Unit Compatibility	Bolt-on tap-off unit from Canalis - KT	
Device Application	High power distribution	
Material	Aluminium	
[le] Rated Operational Current	3200 A at 35 °C	
Polarity	3L + N + PE	
Number Of Tap-Off Outlets	1	
Nominal Output Current	4001250 A	
Earth Conductor	Standard earth	
Short-Circuit Level	Reinforced version	
Length	2000 mm	
Provided Equipment	Trunking unit Jointing unit	

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	113 kA
[lpk] Rated Peak Withstand Current	248 kA
Electrical Connection	Bolted connection
Radiated Magnetic Field	2.1 μΤ
Thermal Stress Limit	12769000 kA².s
Thdi	015 % 3200 A 1533 % 4000 A

Life Is On Schneider Apr 19, 2024

Maximum Voltage Drop	<0.0018 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0019 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0018 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0017 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By hook
Mounting Support	Cantilever arm Pendant
Installation Direction	Horizontal Vertical
Neutral Position	Right
Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Fix
Width	140 mm
Height	324 mm
Colour	White (RAL 9001)
Net Weight	92 kg
Linear Load	46 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	035 °C (100 % of In) 3540 °C (97 % of In) 4045 °C (93 % of In) 4550 °C (90 % of In) 5055 °C (86 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.4 cm
Package 1 Width	14.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	103.2 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information