



Product datasheet

Specifications

Canalis - Al length for plug-in tap-off unit - 3200A - 3L+PE - 4m standard



KTA3200ED340

 **Discontinued on:** Jul 7, 2021

 **Discontinued**

Main

Range	Canalis
Product Name	KT
Product Or Component Type	Busbar trunking
Busbar Description	Distribution length
Device Short Name	KTA
Device Application	High power distribution
Material	Aluminium
[Ie] Rated Operational Current	3200 A at 35 °C
Polarity	3L + PE
Number Of Tap-Off Outlets	3
Nominal Output Current	25...630 A
Earth Conductor	Standard earth
Short-Circuit Level	Standard version
Length	4000 mm
Provided Equipment	Trunking unit Jointing unit

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	86 kA
[Ipk] Rated Peak Withstand Current	189 kA
Electrical Connection	Sliding contact
Radiated Magnetic Field	2.1 µT
Thermal Stress Limit	7396000 kA².s
Thdi	0...15 % 3200 A 15...33 % 4000 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Voltage Drop	<0.0018 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0019 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0018 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0017 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By hook
Mounting Support	Pendant Cantilever arm
Installation Direction	Horizontal Vertical
Neutral Position	Right
Tap-Off Unit Interval	1000 mm
Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Fix
Width	140 mm
Height	324 mm
Colour	White (RAL 9001)
Net Weight	124 kg
Linear Load	31 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (97 % of In) 40...45 °C (93 % of In) 45...50 °C (90 % of In) 50...55 °C (86 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1