

Product datasheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red orange, 60mm, base mounting, steady or flashing, with buzzer 70...85 dB,24V AC DC

XVC6B25SK

❗ Discontinued

❗ Discontinued on: Aug 27, 2020

Main

| | |
|------------------------------------|---|
| Range Of Product | Harmony XVC6 |
| Product Or Component Type | Complete pre-wired monolithic tower light |
| Beacon Or Indicator Bank Unit Type | 2 illuminated units |
| Sound Signalling | Buzzer |
| Mounting Diameter | 60 mm |
| Component Name | XVC |
| Light Source | LED steady or flashing red LED steady or flashing orange |
| [Us] Rated Supply Voltage | 24 V |
| Supply Circuit Type | AC/DC |
| Noise Level | 70...85 dB (continuous or intermittent tone) at 1 m |

Complementary

| | |
|--|--|
| Material | Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover |
| Product Mounting | On base |
| Cable Cross Section | 0.33 mm² |
| Awg Gauge | AWG 22 |
| Cable Length | 850 mm |
| Marking | CE |
| [Uimp] Rated Impulse Withstand Voltage | 0.8 kV |
| Current Consumption | 90 mA |
| Fundamental Frequency | 2.23 kHz |
| Flashing Frequency | 1 Hz |
| Net Weight | 0.25 kg |
| Height | 160.8 mm |

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|--|
| Standards | IEC 61000-6-4 IEC 61000-6-3 IEC 61000-6-2 |
| Product Certifications | UL |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -35...70 °C |
| Ambient Air Temperature For Operation | -10...50 °C |
| Electrical Shock Protection Class | Class II conforming to IEC 61140 |
| Ip Degree Of Protection | IP54 flat surface installation conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.6 cm |
| Package 1 Width | 8.8 cm |
| Package 1 Length | 50.2 cm |
| Package 1 Weight | 480.0 g |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 40.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 7.109 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

| | |
|-------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|-------------------|--|

| | |
|-----------------------|--|
| China Rohs Regulation | China RoHS declaration |
|-----------------------|--|

| | |
|--------------------------|---|
| Environmental Disclosure | Product Environmental Profile |
|--------------------------|---|


| | |
|---------------------|---|
| Circularity Profile | End of Life Information |
|---------------------|---|

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



| No. of illuminated units | b (mm) | b (in.) |
|--------------------------|--------|---------|
| 1 stage | 120.8 | 4.76 |
| 2 stages | 160.8 | 6.33 |
| 3 stages | 200.8 | 7.90 |
| 4 stages | 240.8 | 9.48 |
| 5 stages | 280.8 | 11.06 |

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

