

Lembar data produk

Spesifikasi



earth-leakage module Compact Vigi ME - 300 mA - 200..440 V- 4 poles

29213

⚠ Telah dihentikan pada: 2 Sep 2020

⚠ Dihentikan

Main

Range Of Product	NR100...250 NS100...250
Range	ComPact
Product Or Component Type	Earth leakage add-on block
Device Application	Wiring
Range Compatibility	ComPact Compact NR circuit breaker ComPact ComPact NS circuit breaker
Poles Description	4P
Protected Poles Description	4t
[In] Rated Current	160 A 100 A
Earth-Leakage Add-On Module Name	ME
Earth-Leakage Protection Class	Class A
Residual Earth-Leakage Sensitivity Adjustment Type	Fixed
[I _{ōn}] Residual Earth-Leakage Sensitive Adjustment	0.3 A
Residual Earth-Leakage Time Delay Adjustment Type	Fixed
[Δt] Residual Earth-Leakage Time Delay Adjustment	0...40 ms

Complementary

Network Type	AC
Network Frequency	50/60 Hz
Mounting Support	DIN rail
Electrical Connection To Mcb	By screws
[U _e] Rated Operational Voltage	220...440 V AC 50/60 Hz conforming to IEC 60947-2
Earth-Leakage Protection	With
Maximum Breaking Time	40 ms
Overvoltage Category	Class II
Height	140 mm
Width	236 mm
Depth	86 mm
Net Weight	3.2 kg

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Environment

Electrical Shock Protection Class	Class II
Standards	IEC 60947-2
Product Certifications	KEMA ASEFA LCIE ASTA

Contractual warranty

Warranty	18 months
----------	-----------