Product datasheet

Specifications





TeSys LRD thermal overload relays - 7...10 A - class 10A

LRD14

Main

Range	TeSys TeSys Deca
Product Name	TeSys LRD TeSys Deca
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRD
Relay Application	Motor protection
Product Compatibility	LC1D09 LC1D12 LC1D38 LC1D32 LC1D25 LC1D18
Network Type	AC DC
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Thermal Protection Adjustment Range	710 A
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1

Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories
	Rail, with specific accessories
	Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
Permissible Current	3 A at 120 V AC-15 for signalling circuit
	0.22 A at 125 V DC-13 for signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz for power circuit conforming to IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit
····· ·	4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button: stop
	Blue push-button: reset

Temperature Compensation	-2060 °C	
Connections - Terminals	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm ² solid without cable end	
	Power circuit: screw clamp terminals 1 cable(s) 1.510 mm ² flexible without cable end	
	Power circuit: screw clamp terminals 1 cable(s) 14 mm ² flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 16 mm ² solid without cable end	
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 1.7 N.m - on screw clamp terminals	
Height	66 mm	
Width	45 mm	
Depth	70 mm	
Net Weight	0.124 kg	

Environment

Climatic Withstand	conforming to IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1
Ambient Air Temperature For Storage	-6070 °C
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations: 6 Gn conforming to IEC 60068-2-6 Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7
Dielectric Strength	1.89 kV at 50 Hz conforming to IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495
Product Certifications	IEC UL CSA CCC EAC BV RINA DNV-GL LROS (Lloyds register of shipping) ATEX INERIS UKCA

Packing Units

Unit Tune Of Backage 1	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	7.800 cm
Package 1 Length	9.000 cm
Package 1 Weight	142.000 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.736 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	384
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	67.776 kg

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information