

Lembar data produk

Spesifikasi



iRTH relay-applies a time delay to de-energizing a load-1C/O- Uc 24-240VAC/24VDC

A9E16068

Main

Relay Application	Time delay relay
Time Delay Type	Delays de-energizing of a load
Range	Acti9
Product Name	IRT
Device Short Name	iRTH
Signal Contacts Composition	1 C/O

Complementary

[Ie] Rated Operational Current	8 A at 250 V AC 8 A at 250 V DC 0.01 A at 5 V DC
Impulse Duration	> 100 ms
Local Signalling	LED, flashing for time delay
Type Of Setting	Rotary knob: time delay configuration
Time Delay Range	0.1...360000 s
Accuracy Error	+/- 10 %
Repeat Accuracy	+/- 0.5 %
[Uc] Control Circuit Voltage	24...240 V AC 50/60 Hz 24 V DC
[Us] Rated Supply Voltage	24...240 V AC at 50/60 Hz 24 V DC
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Height	93 mm
Width	18 mm
Depth	72 mm
Net Weight	0.065 kg
Colour	White
Mechanical Durability	5000000 cycles
Electrical Durability	AC-1: 100000 cycles
Undervoltage Behaviour	100 ms

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Connections - Terminals	Tunnel type terminals for 2 cable(s) 1.5 mm² flexible with cable end Tunnel type terminals for 2 cable(s) 1.5 mm² flexible without cable end Tunnel type terminals for 2 cable(s) 2.5 mm² rigid with cable end Tunnel type terminals for 2 cable(s) 2.5 mm² rigid without cable end
-------------------------	--

Environment

Ip Degree Of Protection	IP20
Immunity To Microbreaks	20 ms
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7.4 cm
Package 1 Length	10.2 cm
Package 1 Weight	80 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.639 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)