

Lembar data produk

Spesifikasi



LINERGY DP 3P D.BLK/ COMPACT 250A 27HOLES

04033

⚠ Telah dihentikan pada: 31 Okt 2021

⚠ Dihentikan

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Distribution block
Product Name	Linergy DP
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure Prisma Prisma PH enclosure Prisma Prisma Pack 250 enclosure
Accessory / Separate Part Category	Current distribution accessory
Ip Degree Of Protection	IPxx B

Complementary

Mounting Support	Prisma mounting plate DIN rail
------------------	-----------------------------------

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Installed Device	EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle - horizontal installation
	EasyPact: fixed CVS250 without earth leakage protection - control: toggle - horizontal installation
	EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation
	EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation
	EasyPact: fixed CVS100...160 with earth leakage protection - control: toggle - horizontal installation
	EasyPact: fixed CVS250 with earth leakage protection - control: toggle - horizontal installation
	EasyPact: fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation
	EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation
	EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS250 without earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - vertical installation
	EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - vertical installation
	EasyPact: fixed CVS100...160 with earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS250 with earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - vertical installation
	EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed INS250 - control: direct front rotary handle - horizontal installation
	ComPact: fixed INS250 - control: direct front rotary handle - vertical installation
	ComPact: fixed INS250 - control: lateral handle - vertical installation
	ComPact: fixed INV100 - control: direct front rotary handle - horizontal installation
	ComPact: fixed INV250 - control: direct front rotary handle - horizontal installation
	ComPact: fixed INV250 - control: lateral handle - vertical installation
	ComPact: fixed INV250 - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX100...250 and ammeter without earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX250 without earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX250 with earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation
	ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation
	ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation
	ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation
	ComPact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation
	ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - horizontal installation
	ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - horizontal installation
	ComPact: plug-in NSX250 without earth leakage protection - control: toggle - horizontal installation
	ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation

handle - vertical installation

ComPact: fixed INV100 - control: direct front rotary handle - vertical installation

ComPact: fixed INV200 - control: direct front rotary handle - vertical installation

ComPact: fixed INV160 - control: direct front rotary handle - horizontal installation

ComPact: fixed INV160 - control: direct front rotary handle - vertical installation

ComPact: fixed INV200 - control: direct front rotary handle - horizontal installation

Poles Description	3P
[Ue] Rated Operational Voltage	690 V AC
[Ui] Rated Insulation Voltage	750 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ie] Rated Operational Current	250 A at 40 °C
[Icw] Rated Short-Time Withstand Current	8.5 kA for 1 s
[Ipk] Rated Peak Withstand Current	30 kA
I²T On Activation	72250000 A².s
Connections - Terminals	Supply: direct connection120 mm² Distribution: spring terminal (per phase) , 6 x 4...10 mm² (flexible) Distribution: spring terminal (per phase) , 3 x 6...16 mm² (flexible) Distribution: spring terminal (per phase) , 6 x 4...10 mm² (rigid) Distribution: spring terminal (per phase) , 3 x 6...16 mm² (rigid)
Height	140 mm
Width	105 mm
Depth	64 mm
Net Weight	0.74 kg

Environment

Pollution Degree	3
Overvoltage Category	III
Resistance To Incandescent Wire	960 °C conforming to IEC 60695-2-11
Standards	IEC 60947-7-1 IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product Certifications	ASEFA
Ambient Air Temperature For Operation	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	12.0 cm
Package 1 Length	14.5 cm
Package 1 Weight	720.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	12 cm
Package 2 Width	24 cm
Package 2 Length	34 cm
Package 2 Weight	7.25 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	280

Package 3 Height	102 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	207.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Sertifikasi & Standar

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins