

Lembar data produk

Spesifikasi



window sensor for residual current protection - 470 x 160 mm

33574

Main

Device Short Name	sensor + Vigi cable
Device Application	Power supply
Range Compatibility	Masterpact MasterPact NW ComPact ComPact NS1600b...3200

Complementary

Current Transformer Type	Earth leakage protection
[In] Rated Current	800 A 1000 A 1250 A 1600 A 2000 A 2500 A 3200 A
Height	Inside: 160 mm Outside: 281 mm
Width	Inside: 470 mm Outside: 572 mm
Depth	72 mm
Accessory / Separate Part Category	Spare part for ComPact NS1600b...3200 Spare part for MasterPact NW

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	65.000 cm
Package 1 Length	34.000 cm
Package 1 Weight	18.450 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	9
Package 2 Height	67.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	180.675 kg

Contractual warranty

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Warranty

12 months

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)