

Lembar data produk

Spesifikasi



Residual current protection relay,
VigiPacT RH10M, 500mA,
12/24VAC 50/60Hz, 12/48VDC,
DIN rail mounting

56106

⚠ Dihentikan

⚠ Telah dihentikan pada: 12 Mei 2023

Main

Range	VigiPacT
Device Short Name	RH10M
Product Or Component Type	Residual current protection relay
Relay Application	Protection relay
Mounting Support	DIN rail
Earth-Leakage Protection Class	Type A
Type Of Setting	None
Residual Earth-Leakage Sensitivity Adjustment Type	Fixed
Earth-Leakage Sensitivity	0.5 A
Earth-Leakage Time Delay	Instantaneous
Current Sensors Compatibility	VigiPacT TOA earth leakage current sensor VigiPacT A earth leakage current sensor VigiPacT L earth leakage current sensor
[Ithe] Conventional Enclosed Thermal Current	8 A
Minimum Load	10 mA at 12 V
[Us] Rated Supply Voltage	12...24 V AC 50/60 Hz 55...120 % 12...48 V DC 55...120 %
Power Consumption In Va	4 VA
Monitored Distribution System	1000 V - AC at 50/60 Hz (maximum) 1000 V - AC at 400 Hz (maximum)
Earthing System	TT TN-S IT
[Uimp] Rated Impulse Withstand Voltage	8 kV
Reset	Manual reset

Complementary

Test Function	Local Remote test
Monitoring	Electronics (continuous) Power supply (continuous) Relay/sensor link (continuous)
Type Of Measurement	Earth fault current internal measurement, range: 80...100 %
Tamperproof Of Settings	Protected by sealable cover

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Connections - Terminals	Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12 Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12 Auxiliary power supply: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12 Fault: screw terminal cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12 Fault: screw terminal cable(s) 0.2...4 mm² rigid AWG 24...AWG 12 Fault: screw terminal cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12 Relay test and fault reset: screw terminal cable(s) 0.14...1 mm² flexible AWG 26...AWG 16 Relay test and fault reset: screw terminal cable(s) 0.14...1.5 mm² rigid AWG 26...AWG 16 Relay test and fault reset: screw terminal cable(s) 0.25...0.5 mm² flexible AWG 26...AWG 16 Sensor: screw terminal cable(s) 0.14...1 mm² flexible AWG 26...AWG 16 Sensor: screw terminal cable(s) 0.14...1.5 mm² rigid AWG 26...AWG 16 Sensor: screw terminal cable(s) 0.25...0.5 mm² flexible AWG 26...AWG 16 Voltage presence: screw terminal cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12 Voltage presence: screw terminal cable(s) 0.2...4 mm² rigid AWG 24...AWG 12 Voltage presence: screw terminal cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12
Wire Stripping Length	Auxiliary power supply: 7 mm for top connection Fault: 8 mm for bottom connection Relay test and fault reset: 5 mm for bottom connection Sensor: 5 mm for top connection Voltage presence: 8 mm for bottom connection
Tightening Torque	Auxiliary power supply: 0.6 N.m top Fault: 0.6 N.m bottom Relay test and fault reset: 0.25 N.m bottom Sensor: 0.25 N.m top Voltage presence: 0.6 N.m bottom
9 Mm Pitches	6
Standards	EN/IEC 60947-2 Annex M EN/IEC 60755 UL 1053 CAN/CSA C22.2 No. 144
Width	54 mm
Height	81 mm
Depth	74 mm
Net Weight	0.3 kg
Ip Degree Of Protection	IP40 on front face: conforming to EN/IEC 60529 IP30 on side parts: conforming to EN/IEC 60529 IP20 on connection terminals: conforming to EN/IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Mechanical Robustness	Fire resistance conforming to IEC 60695-2-1 IK protection 2 joules: IK07 conforming to EN 50102 Vibrations 13.2...100 Hz: 0.7 g Vibrations 2...13.2 Hz: +/- 1 mm

Environment

Overvoltage Category	IV
Electrical Shock Protection Class	Class II
Electromagnetic Compatibility	Conducted and radiated emissions: , B, conforming to CISPR 11 Conducted radio-frequency immunity test: , 3, conforming to IEC 61000-4-6 Electrostatic discharge immunity test: , 4, conforming to IEC 61000-4-2 High-energy conducted susceptibility: , 4, conforming to IEC 61000-4-5 Low-energy conducted susceptibility: , 4, conforming to IEC 61000-4-4 Radiated susceptibility: , 3, conforming to IEC 61000-4-3
Relative Humidity	95 % at 55 °C
Pollution Degree	3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-35...70 °C

Ambient Air Temperature For Storage	-55...85 °C
-------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	

Sertifikasi & Standar

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins