

# Lembar data produk

Spesifikasi



## PratiKa wander socket - straight - 63 A - 3P + E - 380...415 V AC - IP67

81482

### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Mureva        |
| Product Or Component Type | Wander socket |
| Device Short Name         | Mureva socket |
| Plug, Socket Category     | Low voltage   |
| Poles Description         | 3P + E        |
| Network Type              | AC            |
| Outlet Standard           | Industrial    |

### Complementary

|                                     |                                                                                   |
|-------------------------------------|-----------------------------------------------------------------------------------|
| Plug, Socket, Control Station Shape | Straight                                                                          |
| [In] Rated Current                  | 63 A                                                                              |
| [Ue] Rated Operational Voltage      | 380...415 V                                                                       |
| Network Frequency                   | 50/60 Hz                                                                          |
| Ground Lug Clockwise Position       | 6 h                                                                               |
| Plug, Socket Material               | Housing: self-extinguishing engineering polymer                                   |
| Contacts Material                   | Pins: stainless steel<br>Sleeves: nickel plated brass<br>Springs: stainless steel |
| Connections - Terminals             | Captive screws                                                                    |
| Cable Cross Section                 | 6...25 mm²                                                                        |
| Cable Outer Diameter                | 17...31 mm                                                                        |
| Cable Entry                         | Cable gland                                                                       |
| Thread Type                         | Pg 36                                                                             |
| Net Weight                          | 0.742 kg                                                                          |
| Height                              | 110 mm                                                                            |
| Width                               | 110 mm                                                                            |
| Depth                               | 265 mm                                                                            |
| Colour                              | Grey (RAL 7035)                                                                   |
| Voltage Colour                      | Red                                                                               |

### Environment

|           |                            |
|-----------|----------------------------|
| Standards | IEC 60309-2<br>IEC 60309-1 |
|-----------|----------------------------|

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                                       |                                                 |
|---------------------------------------|-------------------------------------------------|
| Ip Degree Of Protection               | IP67 conforming to IEC 60529                    |
| Ik Degree Of Protection               | IK08 conforming to EN 62262                     |
| Fire Resistance                       | 850 °C conforming to IEC 60695-2-1              |
| Relative Humidity                     | 50 % at 40 °C<br>70 % at 30 °C<br>90 % at 20 °C |
| Ambient Air Temperature For Operation | 35 °C ( 86400 s )<br>-25...40 °C                |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 10.9 cm  |
| Package 1 Width              | 10.9 cm  |
| Package 1 Length             | 26.5 cm  |
| Package 1 Weight             | 752.0 g  |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 8.007 kg |

## Keberlanjutan

**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

## Kinerja kesejahteraan

 Rohs Exemption Information Yes

## Sertifikasi & Standar

|                          |                                                                                                                       |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                     |
| Eu Rohs Directive        | Compliant with Exemptions                                                                                             |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                         |
| Circularity Profile      | No need of specific recycling operations                                                                              |