

Lembar data produk

Spesifikasi



contactor iCT - 3 poles - 3 NO - 25 A - 220..240 V AC

A9C20833

Main

Range Of Product	Acti9
Product Name	Acti9 iCT
Product Or Component Type	Contacteur
Device Short Name	iCT
Device Application	Motor-heating-lighting
Poles	3P
[Ie] Rated Operational Current	25 A AC-7A 8.5 A AC-7B
Pole Contact Composition	3 NO
Network Type	AC
Control Type	Remote control
[Uc] Control Circuit Voltage	220...240 V AC 50 Hz

Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	400 V AC 50 Hz
Maximum Power	1.6 W at 400 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Signal Type	Maintained
Switching Frequency	100 switching operations/day
Local Signalling	Action indicator
Hold-In Power Consumption In Va	4.6 VA
Inrush Power In Va	34 VA
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	60 mm
Colour	White

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Mechanical Durability	1000000 cycles
Electrical Durability	100000 cycles IEC/EN 61095 25 A 50 Hz AC-7A 30000 cycles IEC/EN 61095 8.5 A 50 Hz AC-7B 30000 cycles IEC/EN 61095 50 Hz AC-7C 100000 cycles EN/IEC 60947-4-1 50 Hz AC-1 30000 cycles EN/IEC 60947-4-1 50 Hz AC-3 30000 cycles EN/IEC 60947-4-1 50 Hz AC-5a 30000 cycles EN/IEC 60947-4-1 50 Hz AC-5b
Connections - Terminals	Control circuit: tunnel type terminals2 cable(s) 1.5 mm² rigid Power circuit: tunnel type terminals1 cable(s) 1...4 mm² flexible Power circuit: tunnel type terminals1 cable(s) 1.5...6 mm² rigid Control circuit: tunnel type terminals1 cable(s) 1.5...2.5 mm² rigid Control circuit: tunnel type terminals2 cable(s) 1.5...2.5 mm² flexible
Tightening Torque	Control circuit: 0.8 N.m Power circuit: 0.8 N.m
Product Compatibility	IACTc IACTp IACTs IATEt
Compatibility Code	ICT
Market Segment	Small commercial Residential

Environment

Standards	IEC/EN 61095
Noise Level	30 dB
Heat Dissipation	1.6 W at 50/60 Hz
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2
Tropicalisation	2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-5...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	11.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	227.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	11.500 cm
Package 2 Width	12.500 cm
Package 2 Length	25.000 cm

Package 2 Weight	1.437 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.043 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations