

Lembar data produk

Spesifikasi



iPRD8 modular surge arrester - 1P - 350V

A9L08100

⚠ Telah dihentikan pada: 1 Nov 2020

⚠ Dihentikan

Main

Range Of Product	Acti9
Product Name	Acti9 iPRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iPRD8
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	NF KEMA-KEUR
Poles Description	1P
Remote Signalling	Without
Surge Arrester Type	Electrical distribution network
Earthing System	TN-C IT 230

Complementary

Surge Arrester Class Type	Type 2 + 3
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 2.5 kA (L/PE) Common mode: 2.5 kA (N/PE)
[Imax] Maximum Discharge Current	Common mode: 8 kA L/PE
[Uoc] Open Circuit Voltage	10 kV type 3 common mode L/PE
[Uc] Maximum Continuous Operating Voltage	Common mode: 350 V L/PE Common mode: 350 V N/PE
Maximum [Up] Voltage Protection Level	Common mode <1 kV type 2 L/PE Common mode <1 kV type 3 L/PE
[Ut] Temporary Overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode
Disconnecter Device Type	Associated circuit breaker iC60L 10 A curve C - Icu 25 kA Associated circuit breaker IC60N 10 A curve C - Icu 10 kA Associated circuit breaker iC60H 10 A curve C - Icu 15 kA Associated fuse gG 25 A - Icu 15 kA Associated fuse gG 80 A - Icu 50 kA

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	2
Height	85 mm
Width	18 mm
Depth	69 mm
Net Weight	0.11 kg
Colour	White (RAL 9003)
[Ipe] Ground Residual Current	0.003 mA 0.6 mA
Connections - Terminals	Tunnel type terminal (downside) 2.5...35 mm² Tunnel type terminal (upside) 2.5...35 mm²
Tightening Torque	2.5 N.m

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	5...95 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	7.2 cm
Package 1 Length	9.2 cm
Package 1 Weight	129 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	10 cm
Package 2 Length	28 cm
Package 2 Weight	1.635 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	15.229 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information