

Lembar data produk

Spesifikasi



single phase power supply,
100...240V input, 24V DC output,
35W, 1,5A

ABL2REM24015K

Main

Range Of Product	Easy Modicon ABL2
Product Or Component Type	Power supply
Power Supply Type	Regulated switch mode
Rated Power In W	36 W
Main Input Voltage	100...240 V AC single phase
Output Voltage	24 V DC
Power Supply Output Current	1.5 A
Operating Position	Any position
Vibration Resistance	4 gn (f= 10...500 Hz) conforming to IEC 61131-2
Name Of Test	Electromagnetic hypersensitivity (EHS) conforming to IEC 61000-6-2 level A

Complementary

Input Voltage Limits	85...264 V
Network Frequency	47...63 Hz
Inrush Current	45 A at 100...240 V AC
Cos Phi	0.45
Efficiency	87 %
Power Dissipation In W	5.4 W
Current Consumption	0.4 A at 240 V
Input Protection Type	Integrated fuse (not interchangeable)
Output Voltage Limits	20.4...27.6 V
Line And Load Regulation	+/- 1 %
Holding Time	>= 12 ms at 115 V
Output Protection Type	Against overload, protection technology: 1.1...1.5 x In Against short-circuits, protection technology: 1.1...1.5 x In Against overvoltage, protection technology: 28.8...33.6 V
Connections - Terminals	For ground connection: screw type terminals, connection capacity: 1 x 4 mm ² AWG 12
Marking	CE
Electromagnetic Compatibility	Immunity to electromagnetic interference conforming to EN 55022 class B
Mounting Support	DIN rail with accessory Panel mounting with accessory
Operating Altitude	5000 m

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Output Coupling	Series
Overvoltage Category	II
Meantime Between Failure [Mtbf]	600000 h at 25 °C
Status Led	1 LED (green) output voltage
Width	99 mm
Height	82 mm
Depth	30 mm
Net Weight	0.23 kg

Environment

Product Certifications	EAC IC RoHS KC RCM
Ip Degree Of Protection	IP20 conforming to IEC 62368-1
Ambient Air Temperature For Operation	-30...70 °C (with power derating of 2.5 % per °C)
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	10...95 %
Overvoltage Category	Class I conforming to IEC 62368-1
Pollution Degree	2
Dielectric Strength	2000 V between input and ground

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.744 cm
Package 1 Width	8.79 cm
Package 1 Length	10.549 cm
Package 1 Weight	231.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	63
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	15.19 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)



Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Dimensions Drawings

Dimensions Drawings


Mechanical Dimensions



Mounting and Clearance

Mounting and Clearance


Vertical Mounting



Horizontal Mounting




Clearance



Performance Curves


Performance Curves

Static Characteristics



- (y) Load %
- (x) Input voltage (VAC) 50/60 Hz

Derating Curve



- (y) Load %
- (x) Ambient temperature (°C)