

Lembar data produk

Spesifikasi



voltage transformer - 230..400 V - 2 x 115 V - 100 VA

ABT7PDU010G

⚠ Telah dihentikan pada: 21 Nov 2022

⚠ Berakhirnya layanan segera pada: 1 Jun 2025

⚠ Dihentikan

Main

Range Of Product	Modicon Transformer Universal
Product Or Component Type	Safety and isolation transformer
Rated Power In Va	100 VA
Input Voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2
Output Voltage	115/230 V AC
Secondary Winding	Double
Protective Cover	With
Ambient Air Temperature For Operation	-20...60 °C

Complementary

Input Voltage Limits	360...440 V 207...253 V
Network Frequency Limits	47...63 Hz
Input Voltage Tolerance	+/- 15 V
Efficiency	86 %
Power Dissipation In W	16.3 W
Voltage Variation At Nominal Load	4 % at 230 V 0,0417 at 400 V
Output Sustained Overvoltage	0,049 (no load, hot state)
Maximum Voltage Drop At Rated Load	4.23 %
No Load Losses	11.26 W
Short-Circuit Voltage	0,062
Output Protection Type	Against overload, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection Against overvoltage, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection Against short-circuits, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection
Connections - Terminals	For input connection: screw type terminals, connection capacity: 5 x 4 mm ² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm ² AWG 11 For output connection: screw type terminals, connection capacity: 4 x 4 mm ² AWG 11
Marking	CE

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Fixing Mode	By 4 screws diameter: 5.5 mm on vertical panel, operating position: horizontal By 4 screws diameter: 5.5 mm on vertical panel, operating position: vertical By clips on 35 x 15 mm symmetrical DIN rail By 4 screws diameter: 5.5 mm on horizontal panel with derating to 90 %
Output Coupling	Grounding of secondary Parallel Series by internal jumper
Operating Altitude	3000 m
Electrical Insulation Class	Class B
Status Led	1 LED (orange) input voltage
Width	87.0 mm
Height	108.0 mm
Depth	138.0 mm
Net Weight	2.86 kg

Environment

Product Certifications	UR EAC DNV-GL
Standards	UL 506
Ip Degree Of Protection	IP20
Environmental Characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-4
Ambient Air Temperature For Storage	-40...80 °C
Relative Humidity	0...95 % during operation
Overvoltage Category	Class I conforming to VDE 0106-1
Dielectric Strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.500 cm
Package 1 Width	18.500 cm
Package 1 Length	11.600 cm
Package 1 Weight	3.182 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	30
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	108.460 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan


✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile

Dimensions Drawings

Dimensions



Dimensions in mm


a	b	c	G	J	Ø
87	138	108	60	96	5.5

Dimensions in in.


a	b	c	G	J	Ø
3.42	5.43	4.25	2.36	3.78	0.22

Connections and Schema


Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring



J2, J3, J4 Internal Jumper