

Lembar data produk

Spesifikasi



Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19

AP8459EU3

Overview

Presentation	APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection. Current metering provides real-time remote monitoring of connected loads. Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Lead Time	Usually in Stock

Main

Colour	Black
Pdu Type	Metered outlet
Cord Length	3.00 m
Provided Equipment	CAN port terminator Installation guide Rack mounting brackets Safety guide Serial configuration cable

Complementary

Input Voltage	200 V 208 V 230 V
Height	182.9 cm
Width	5.6 cm
Output Voltage	230 V
Depth	5.1 cm
Net Weight	6.76 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	100...240 V

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Input Current Limits	16 A
Load Capacity	3700 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product Certifications	UL listed VCCI class A VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Ambient Air Temperature For Operation	-5...60 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203.7 cm
Package 1 Width	16.3 cm
Package 1 Length	11.7 cm
Package 1 Weight	9.03 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Efisien Energi Take-back Transparansi RoHS/REACH

Kinerja sumber daya

✓

Energy Efficient Product

✓

Take-Back Program Available

Kinerja kesejahteraan

✓

Lead Free

✓

Mercury Free

✓

Rohs Exemption Information

Yes

Sertifikasi & Standar

Reach Regulation

REACH Declaration

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

End of Life Information