

Lembar data produk

Spesifikasi



S-Classic - 1-way switch - 1 gang - white

E31_1_2AR_WE_G3_B

Main

Range	S-Classic
Product Or Component Type	Switch
Device Application	Control
Switch Application	Lighting
Quantity Per Set	Set of 1

Complementary

Control Type	Rocker
Actuator	Rocker
Switch Function	1-way
Number Of Gangs	1 gang
Device Mounting	Flush Surface
Rated Current	10 AX at 250 V AC
Number Of Terminals	2
Material	Plate: PC (polycarbonate), white Dolly: PC (polycarbonate), white Base: PA66, black
Embedding Depth	12.3 mm
Height	87 mm
Width	87 mm
Depth	28.9 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	GB 16915.1 IEC 60669-1 SS 227-1 MS IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	2.89 cm
Package 1 Weight	0.001 g

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations