


Lembar data produk

Spesifikasi



RISER FOOT WITH FIRE BARRIER

KSA630EV4AF

⚠ Telah dihentikan pada: 7 Jul 2021

⚠ Dihentikan

Main

Range	Canalis
Device Short Name	KSA
Product Or Component Type	Busbar trunking
Busbar Description	Riser foot Fire barrier
Device Application	Rise medium power distribution
Conductors Material	Aluminium
Busbar Trunking Polarity	3L + N + PE
Number Of Tap-Off Outlets	0
[Ie] Rated Operational Current	630 A at 35 °C
Mounting Mode	By screws
Dimension Type	Fix

Complementary

Neutral Position	Right
Mounting Position	Vertical - neutral on right
[Ue] Rated Operational Voltage	230...690 V
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	690 V
[Icw] Rated Short-Time Withstand Current	32.1 kA
[Ipk] Rated Peak Withstand Current	67.5 kA
Electrical Connection	Lubricated sliding contact
Width	124 mm
Depth	255 mm
Height	1150 mm
Net Weight	25 kg
Maximum Load	1760 kg
Radiated Magnetic Field	0.89 µT
Thermal Stress Limit	1225000 kA².s

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Thdi	0...15 % 630 A 15...33 % 500 A 33...100 % 400 A
Maximum Voltage Drop	<0.011 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.013 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.013 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.012 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	IEC 61439-1 IEC 61439-6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------