

Lembar data produk

Spesifikasi



TeSys D - time delay auxiliary contact block - 1 NO + 1 NC screw clamp terminals

LADT2

Main

Range	TeSys TeSys Deca
Product Name	TeSys Deca
Product Or Component Type	Time delay auxiliary contact block
Range Compatibility	TeSys Deca CAD TeSys Deca LC1D TeSys F LC1F TeSys F CR1F
Mounting Location	Front
Pole Contact Composition	1 NO + 1 NC
Contacts Operation	Time delay
Timer Type	On delay
Time Delay Range	1...30 s
[Ue] Rated Operational Voltage	690 V AC 25...400 Hz
[Ie] Rated Operational Current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C)
Standards	CSA C22.2 No 60947-5-1 GB/T 14048.5 EN/IEC 60947-5-1
Product Certifications	IECEE CB Scheme UL CSA CCC EAC UKCA

Complementary

Irms Rated Making Capacity	140 A at <= 690 V AC conforming to IEC 60947-5-1 250 A at <= 690 V DC conforming to IEC 60947-5-1
Permissible Short-Time Rating	100 A 60 °C 1 s 120 A 60 °C 500 ms 140 A 60 °C 100 ms
Protection Type	GG fuse 10 A
Mechanical Durability	5 Mcycles

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Non-Overlap Time	1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact
Insulation Resistance	> 10 MOhm
Connections - Terminals	Screw clamp terminals 1 cable(s) 1...2.5 mm²flexible with cable end Screw clamp terminals 1 cable(s) 1...2.5 mm²flexible without cable end Screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 1...2.5 mm²flexible without cable end Screw clamp terminals 1 cable(s) 1...2.5 mm²rigid Screw clamp terminals 2 cable(s) 1...2.5 mm²rigid Screw clamp terminals
Tightening Torque	1.7 N.m - with screwdriver flat Ø 6 mm 1.7 N.m - with screwdriver Philips No 2 1.7 N.m - with screwdriver pozidriv No 2
Height	48 mm
Width	44 mm
Depth	61 mm
Colour	Dark grey

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068
Ambient Air Temperature For Storage	-60...80 °C
Ambient Air Temperature For Operation	-40...70 °C
Operating Altitude	3000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	6.5 cm
Package 1 Length	5 cm
Package 1 Weight	74 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.2 cm
Package 2 Width	13 cm
Package 2 Length	24 cm
Package 2 Weight	752 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	140
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	11 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations