

# Lembar data produk

Spesifikasi



## TeSys LE - enclosed DOL starter - 3.7...5.5 A - 380 V AC coil

LE1M35Q712

### Main

|                                     |                                                                                                                                   |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Range                               | TeSys                                                                                                                             |
| Product Name                        | TeSys LE                                                                                                                          |
| Device Short Name                   | LE1M                                                                                                                              |
| Product Or Component Type           | Enclosed DOL starter                                                                                                              |
| Device Application                  | Standard                                                                                                                          |
| Utilisation Category                | AC-3                                                                                                                              |
| Device Composition                  | Contactor<br>Earth terminal<br>Neutral terminal<br>Thermal overload relay                                                         |
| Thermal Protection Adjustment Range | 3.7...5.5 A                                                                                                                       |
| Motor Power Kw                      | 0.75 kW at 240 V AC 50/60 Hz<br>2.2 kW at 415 V AC 50/60 Hz<br>1.1 kW at 220/230 V AC 50/60 Hz<br>2.2 kW at 380/400 V AC 50/60 Hz |
| [Uc] Control Circuit Voltage        | 380 V AC 50/60 Hz                                                                                                                 |
| Control Type                        | Push-button start green I<br>Push-button stop/reset red O                                                                         |

### Complementary

|                    |                                                                                                                                                                   |
|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Local Signalling   | Operating: LED (yellow)                                                                                                                                           |
| Cable Entry Number | 2 ISO20 top<br>2 ISO25 top<br>2 Pg 13 top<br>2 Pg 21 top<br>2 ISO20 bottom<br>2 ISO25 bottom<br>2 Pg 13 bottom<br>2 Pg 21 bottom<br>2 Pg 16 top<br>2 Pg 16 bottom |
| Width              | 78 mm                                                                                                                                                             |
| Height             | 160 mm                                                                                                                                                            |
| Depth              | 108 mm                                                                                                                                                            |
| Net Weight         | 0.6 kg                                                                                                                                                            |

### Environment

|                         |                                       |
|-------------------------|---------------------------------------|
| Material                | ABS (acrylonitrile butadiene-styrene) |
| Ip Degree Of Protection | IP65 conforming to IEC 60529          |

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                                       |                      |
|---------------------------------------|----------------------|
| Standards                             | IEC 60947-4-1        |
| Ambient Air Temperature For Operation | -5...40 °C           |
| Environmental Characteristic          | Standard environment |
| Product Certifications                | UKCA                 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 11.600 cm |
| Package 1 Width              | 16.600 cm |
| Package 1 Length             | 8.200 cm  |
| Package 1 Weight             | 572.900 g |
| Unit Type Of Package 2       | S02       |
| Number Of Units In Package 2 | 6         |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 3.766 kg  |
| Unit Type Of Package 3       | P06       |
| Number Of Units In Package 3 | 96        |
| Package 3 Height             | 75.000 cm |
| Package 3 Width              | 60.000 cm |
| Package 3 Length             | 80.000 cm |
| Package 3 Weight             | 70.788 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

### Kinerja kesejahteraan

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |

### Sertifikasi & Standar

|                          |                                                                                                                             |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                           |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>                                                                            |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>                                                                                      |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                               |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | <a href="#">End of Life Information</a>                                                                                     |