

Lembar data produk

Spesifikasi



TeSys LT47 electronic over current relays - manual - 3...30 A - 200...240 V AC

LT4730M7S

Main

Range	TeSys
Product Name	TeSys LT
Product Or Component Type	Electronic over current relay
Device Short Name	LT47
Device Application	Protection
Relay Application	Locked rotor, mechanical jamming $I > 3 \times I_{setting}$ Overload $I_{max} > I_{setting}$ Sensitivity to phase failure
[Us] Rated Supply Voltage	200...240 V AC
Thermal Protection Adjustment Range	3...30 A
[Ui] Rated Insulation Voltage	Power circuit: 600 V AC conforming to CSA Power circuit: 600 V AC conforming to UL Power circuit: 690 V AC conforming to IEC 60947-4-1

Complementary

Network Frequency	50...60 Hz
Mounting Support	Rail
Tripping Threshold	3...25 A
Electromagnetic Compatibility	Resistance to electrostatic discharge: 8 kV in open air conforming to IEC 61000-4-2 Resistance to electrostatic discharge: 6 kV in direct mode conforming to IEC 61000-4-2 Conducted emission: class A conforming to EN 55011 Immunity to electromagnetic interference: 10 V/m conforming to IEC 61000-4-3 Immunity to fast transients: 2 kV conforming to IEC 61000-4-4 Surge withstand: 6 kV conforming to IEC 61000-4-5 Conducted HF disturbances: 10 V conforming to IEC 61000-4-6
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	3 A for signalling circuit
Associated Fuse Rating	3 A gG for signalling circuit 3 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Time Range	0.5...30 s - control type D-time 0.3...10 s - control type O-time
Local Signalling	1 LED (green) 1 LED (red)
Control Type	push-button: reset electrical: reset

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Connections - Terminals	Signalling circuit: screw clamp terminals 1 1...2.5 mm² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 1 1...2.5 mm² - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible without cable end
Tightening Torque	Signalling circuit: 1.7 N.m M3.5
Height	70.3 mm
Width	71 mm
Depth	77.2 mm
Net Weight	0.192 kg

Environment

Standards	IEC 60255-6 IEC 60947
Product Certifications	UL CSA
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-25...60 °C without derating conforming to IEC 60947-4-1
Ambient Air Temperature For Storage	-30...80 °C
Operating Altitude	2000 m
Mechanical Robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 4 gn conforming to IEC 60068-2-6
Dielectric Strength	2 kV at 50 Hz conforming to IEC 60255-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	7.800 cm
Package 1 Length	8.700 cm
Package 1 Weight	197.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	16
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.620 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)