

Lembar data produk

Spesifikasi



circuit breaker Compact NSXm
63A 3P 25kA at 380/415V(IEC)
compression lug

LV426255

⚠ Telah dihentikan pada: 15 Jun 2023

⚠ Dihentikan

Main

Range	ComPact
Product Name	ComPact NSXm
Range Of Product	ComPact NSXm
Device Short Name	NSXm 63B
Product Or Component Type	Circuit breaker
Device Application	Protection Distribution
Number Of Poles	3P
Protected Poles Description	3D
[In] Rated Current	63 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	B 25 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	By screws Clip-on

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ics] Rated Service Short-Circuit Breaking Capacity	50 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles at 440 V In 20000 cycles at 440 V In/2 5000 cycles at 690 V In 10000 cycles at 690 V In/2
Mounting Support	Plate DIN rail
Connection Terminals	compression lug/busbar
Connection Pitch	35 mm with spreaders 27 mm without spreaders
9 Mm Pitches	9 module
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	63 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Im] Magnetic Protection Pick-Up Range	800 A
Earth-Leakage Protection	Without
Number Of Slots For Electrical Auxiliaries	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
Width (W)	81 mm
Height (H)	137 mm
Depth (D)	80 mm
Net Weight	1.06 kg
Colour	Grey (RAL 7016)

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm

Package 1 Width	12 cm
Package 1 Length	21.5 cm
Package 1 Weight	1.111 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.45 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	216
Package 3 Height	105 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	262.8 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan



Mercury Free



Rohs Exemption Information

Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations