

Lembar data produk

Spesifikasi



circuit breaker Compact NSX100H - TMD - 100 A - 4 poles 3d

LV429680

⚠ Telah dihentikan pada: 15 Jun 2023

⚠ Dihentikan

Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100...250
Device Short Name	NSX100H
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	4P
Protected Poles Description	3t
Neutral Position	Left
[In] Rated Current	100 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	10 kA at 600 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 65 kA at 480 V AC 50/60 Hz conforming to UL 508 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	H 70 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

[Ics] Rated Service Short-Circuit Breaking Capacity	10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	50000 cycles
Electrical Durability	10000 cycles at 690 V In 20000 cycles at 690 V In/2 30000 cycles at 440 V In 50000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	100 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	120...400 s at 1.5 x In 15 s at 6 x Ir
Short-Time Protection Pick-Up Adjustment Type Isd	Fixed
[Isd] Short-Time Protection Pick-Up Adjustment Range	800 A
Short-Time Protection Delay Adjustment Type Tsd	Fixed
Earth-Leakage Protection	Without
Neutral Protection Settings	No protection (3t)
Number Of Slots For Electrical Auxiliaries	5 slot(s)
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm
Net Weight	2.4 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C

Ambient Air Temperature For Storage	-50...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.5 cm
Package 1 Width	16.86 cm
Package 1 Length	19.0 cm
Package 1 Weight	2.313 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information