

Lembar data produk

Spesifikasi



Anti Harmonic detuned reactor 100kvar 190Hz (3.8) 7% 50Hz 400V

LVR07X00A40T

Main

Range	PowerLogic
Device Short Name	DR
Product Or Component Type	Detuned reactor
Network Frequency	50 Hz
Reactive Power Rating	100 kvar for 400 V AC 50 Hz
Network Rated Voltage	400 V AC 50 Hz
Tuning Order	3.8 - 190 Hz - 7 % - 50 Hz

Complementary

Power Losses (Max)	480 W
Value Of Inductance	0.375 mH
Inductance Tolerance	- 5 % to 5 % per phase
Fundamental Current Rating	144.3 A
Rms Current Rating	155.9 A
Electrical Insulation Class	Class H
[Ui] Rated Insulation Voltage	1.1 kV
Dielectric Test Voltage	4 kV 50 Hz 1 minute
[Imp] Maximum Permanent Current	1.2 x I1
Harmonic Current Spectrum	3.7 % x I3 38.2 % x I5 13.6 % x I7 4.9 % x I11
Dynamic Withstand Current	2.2 x Isc
[Ith] Conventional Free Air Thermal Current	2 A at 250 V AC 50 Hz
Type Of Installation	Indoor installation
Type Of Cooling	Forced convection
Connections - Terminals	Pad terminal
Fixing Center	200 x 125 mm
Height	350 mm
Width	350 mm
Depth	220 mm
Net Weight	37 kg

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Environment

Standards	IEC 60068
Ip Degree Of Protection	IP00
Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	0...55 °C at <= 1000 m 0...50 °C at > 1000...2000 m
Average Ambient Air Temperature For Operation	50 °C at <= 1000 m (average over 24 hours) 40 °C at <= 1000 m (average over 1 year) 45 °C at > 1000...2000 m (average over 24 hours) 35 °C at > 1000...2000 m (average over 1 year)
Climatic Withstand	Relative humidity: 20...80 % Salt mist (400 V/50 Hz) : 250 hours

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	56.0 cm
Package 1 Width	40.0 cm
Package 1 Length	60.0 cm
Package 1 Weight	44.0 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	2
Package 2 Height	50.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	96.5 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations