

Lembar data produk

Spesifikasi



PM5330 powermeter w modbus -
upto 31st H - 256K 2DI/2DO
35alarms - flush mount

METSEPM5330

Main

Range	PowerLogic
Product Name	PowerLogic PM5000
Device Short Name	PM5330
Product Or Component Type	Power meter

Complementary

Power Quality Analysis	up to the 31st harmonic
Device Application	Power monitoring Multi-tariff
Type Of Measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply Voltage	90...450 V AC 45...65 Hz 100...300 V DC
Network Frequency	50 Hz 60 Hz
[In] Rated Current	1 A 5 A
Type Of Network	3P + N 3P 1P + N
Maximum Power Consumption In Va	11 VA at 415 V
Ride-Through Time	80 ms 120 V AC typical 100 ms 230 V AC typical 100 ms 415 V AC typical 50 ms 125 V DC typical
Display Type	Monochrome graphic LCD
Display Resolution	128 x 128 pixels
Sampling Rate	64 samples/cycle
Measurement Current	5...8500 mA
Analogue Input Type	Voltage (impedance 5 MOhm) Current (impedance <= 0.3 mOhm)
Measurement Voltage	35...760 V AC 45...65 Hz between phases 20...400 V AC 45...65 Hz between phase and neutral
Frequency Measurement Range	45...65 Hz
Number Of Inputs	2 digital

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Measurement Accuracy	Active energy +/- 0.5 % Reactive energy +/- 2 % Active power +/- 0.5 % Apparent power +/- 0.5 % Frequency +/- 0.05 % Power factor +/- 0.5 Current +/- 0.5 % Voltage +/- 0.5 % Apparent energy +/- 0.5 % Reactive power +/- 2 %
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22
Number Of Outputs	2 relay 2 digital
Information Displayed	Tariff (4)
Communication Port Protocol	Modbus RTU and ASCII at 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires, insulation 2500 V JBUS
Communication Port Support	RS485
Data Recording	Maintenance logs Time stamping Alarm logs Data logs Min/max of instantaneous values Event logs
Memory Capacity	256 kB
Connections - Terminals	Voltage circuit: screw terminal block4 Control circuit: screw terminal block2 Current transformer: screw terminal block6 Input/output circuit: screw terminal block6 Relay output: screw terminal block4 Ethernet network: RJ45 connector
Mounting Mode	Flush-mounted
Mounting Support	Framework
Standards	UL 61010-1 IEC 62053-22:2020 IEC 61557-12:2015 EN 50470-3 IEC 60529 IEC 62053-24 EN 50470-1 IEC 62053-23:2020 IEC 62052-11:2020 IEC 62052-31:2015
Product Certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1
Width	96 mm
Depth	72 mm
Height	96 mm
Net Weight	430 g

Environment

Electromagnetic Compatibility	Conducted and radiated emissions class B conforming to EN 55022 Immunity to conducted disturbances - test level: 150 kHz...80 MHz level 4 conforming to IEC 61000-4-6 Electrical fast transient/burst immunity test level 3 conforming to IEC 61000-4-4 Radiated radio-frequency electromagnetic field immunity test level 4 conforming to IEC 61000-4-3 Voltage dips and interruptions immunity test class B conforming to IEC 61000-4-11 Limits for harmonic current emissions class A conforming to IEC 61000-3-2 Electrostatic discharge level 4 conforming to IEC 61000-4-2 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency level 4 conforming to IEC 61000-4-8 Immunity to conducted disturbances - test level: 150 kHz...80 MHz conforming to IEC 61000-4-6 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Limitation of voltage changes, voltage fluctuations and flicker in low-voltage conforming to IEC 61000-3-3 Electrostatic discharge - test level: 8 kV level 4 conforming to IEC 61000-4-2
Ip Degree Of Protection	IP54 display: conforming to IEC 60529 IP30 rear: conforming to IEC 60529
Relative Humidity	5...95 % at 50 °C non-condensing
Pollution Degree	2
Ambient Air Temperature For Operation	-25...70 °C meter
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	2000 m CAT III 3000 m CAT II

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	12.6 cm
Package 1 Length	12.6 cm
Package 1 Weight	550.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.6 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	206.4 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)