


Lembar data produk

Spesifikasi



Terminal block, Linergy TR, push-in type, feed through, 3 points, 4mm², blue, set of 50

NSYTRP43BL

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Terminal block
Device Short Name	TRP
Accessory / Separate Part Category	Connection accessory
Terminal Block Type	Passthrough
Terminal Block Level	1
Mounting Mode	Clip-on
Nominal Cross Section	4 mm ²
Length	66.5 mm
Colour	Blue
Quantity Per Set	Set of 50

Complementary

Width	6.2 mm
Height	36.5 mm
Connections - Terminals	1 x push-in: upstream 2 x push-in: downstream
Number Of Connections	3
Connection Position	Top
Number Of Measurement Input	2
Cable Cross Section	0.2...4 mm ² , flexible without cable end 0.2...6 mm ² , solid with cable end 0.8...4 mm ² , flexible with cable end 0.2...4 mm ² , solid without cable end
Wire Stripping Length	12 mm
Tool Type	Connection: without tool Disconnection: flat screwdriver
[Ue] Rated Operational Voltage	800 V conforming to EN/IEC 60947-7-1 600 V CSA 600 V cURus
[In] Rated Current	32 A conforming to EN/IEC 60947-7-1 30 A CSA 30 A cURus

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Material	Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring
Dielectric Loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric Constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface Resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30
Creep Resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30
Flame Retardance	V0, thickness 0.8 mm conforming to UL 94
Net Weight	11.3 g
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product Compatibility	Spacial enclosures

Environment

Product Certifications	cURus ATEX CSA EAC IEC-Ex LR GL
Dielectric Strength	1000 V conforming to IEC 60243-1
Ambient Air Temperature For Operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.762 cm
Package 1 Width	3.556 cm
Package 1 Length	6.858 cm
Package 1 Weight	9.072 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	5 cm
Package 2 Width	7 cm
Package 2 Length	27 cm
Package 2 Weight	615 g

Contractual warranty

Warranty

18 months

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations