


Lembar data produk

Spesifikasi



Terminal block, Linergy TR, push-in type, basic disconnect terminal, 2 points, 4mm², grey, set of 50

NSYTRP42TB

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Terminal block
Device Short Name	TRP
Terminal Block Type	Removable carrier disconnect
Associated Connection Component	Diode Cylindrical fuse Blade
Terminal Block Level	1
Mounting Mode	Clip-on
Nominal Cross Section	4 mm ²
Length	56 mm
Colour	Grey
Quantity Per Set	Set of 50

Complementary

Fuse Size	5 x 20 mm 6 x 32 mm
Width	6.2 mm
Height	36.5 mm
Connections - Terminals	1 x push-in: upstream 1 x push-in: downstream
Number Of Connections	2
Connection Position	Top
Number Of Measurement Input	2
Cable Cross Section	0.2...4 mm ² , flexible without cable end 0.2...6 mm ² , solid
Wire Stripping Length	10 mm
Tool Type	Disconnection: flat screwdriver Connection: without tool
[Ue] Rated Operational Voltage	400 V conforming to EN/IEC 60947-7-1 300 V cURus 300 V CSA
[In] Rated Current	20 A conforming to EN/IEC 60947-7-1 20 A cURus 20 A CSA

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Material	Polyamide 6/6: insulating case
Dielectric Loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric Constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface Resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30
Creep Resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30
Flame Retardance	V0, thickness 0.8 mm conforming to UL 94
Net Weight	9.3 g
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product Compatibility	Spacial enclosures

Environment

Product Certifications	CSA EAC cURus VDE GL
Dielectric Strength	1000 V conforming to IEC 60243-1
Ambient Air Temperature For Operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	3.5 cm
Package 1 Length	5.7 cm
Package 1 Weight	8.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	4.8 cm
Package 2 Width	6.8 cm
Package 2 Length	32 cm
Package 2 Weight	434 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	1000
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	9.188 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations