

Product datasheet

Specifications



Acti9 - IHP - digital time switch - 24 hours + 7 days - 3 years memory

15854

 **Discontinued on:** 31 Dec 2015

 **Discontinued**

Main

Range Of Product	Acti9
Product Name	Acti9 IHP
Device Short Name	IHP
Product Or Component Type	Programmable digital time switch
Device Application	Building
Battery Type	Lithium
Number Of Channels	1
Language	Danish Norwegian English Swedish French Finnish Dutch
Colour Tint	White (RAL 9003)

Complementary

Power Consumption In Va	2.5 VA
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Accuracy	+/- 1 s/day 20 °C
Cycle Duration	24 hours + 7 days
Maximum Number Of Switchings	28
Minimum Interval Duration	1 min
Function Available	Automatic winter/summer time changeover
Display Type	Backlit LCD
Battery Life	5 year(s)
Backup Time	3 years time and program saving
Connections - Terminals	screw terminals
Mounting Support	DIN rail
9 Mm Pitches	2
Width	18 mm
Height	85 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	66 mm
Function	None
Absence For Holidays	No
Time Changeover	Automatic
Updated By	None
Compatibility Code	IHP

Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2.8 cm
Package 1 Length	10.5 cm
Package 1 Weight	0.132 kg

Contractual warranty

Warranty	18 months
----------	-----------