

Lembar data produk

Spesifikasi



Schneider Electric On-Line UPS 2000VA, 230V, 6x IEC 60320 C13 & 2x IEC Jumpers outlets

SR12KXIET

Overview

Presentation	Proven Industrial UPS power protection for control applications and harsh environments.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	1400 W
Rated Power In Va	2000 VA
Input Connection Type	BS1363A British IEC 60320 C20 Schuko CEE 7 / EU1-16P
Output Connection Type	6 IEC 60320 C13 2 IEC Jumpers
Number Of Rack Unit	2U
Cable Length	2.44 m
Number Of Cables	1
Provided Equipment	CD with software Smart UPS signalling RS-232 cable User manual

Batteries & Runtime

Run-Time	View Runtime Graph
Efisiensi	View Efficiency Graph
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	1
Number Of Battery Free Slots	0
Battery Recharge Time	4 h
Number Of Battery Replacement Quantity	1
Battery Charger Power	79 W rated
Battery Life	3...5 year(s)

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Replacement Battery	RBC31 
Extended Runtime	1

General

Ups Type	Double conversion online
Number Of Power Module	1400
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	8.5 cm
Depth	48.3 cm
Net Weight	25 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz +/- 5 Hz auto-sensing
Input Voltage Limits	160...280 V

Output

Maximum Configurable Power In Va	2000 VA
Maximum Configurable Power In W	1400 W
Output Frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 3 %
Crest Factor	3 : 1
Bypass Type	Built-in bypass
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage

Conformance

Product Certifications	C-Tick CE GOST VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...15240.00 m
Acoustic Level	50 dBA
Heat Dissipation	543 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off	Optional

Surge Protection and Filtering

Surge Energy Rate	420 J
Noise Suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	28.6 cm
Package 1 Width	63 cm
Package 1 Length	59.4 cm
Package 1 Weight	29.82 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	117 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	225 kg

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
----------	--

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins