Product datasheet

Specifications

, → Green Premium[™]



C60 - circuit breaker - C60H - 4P - 20A - C curve

25014

() Discontinued on: 10 Dec 2018

(!) Discontinued

Main

Mann	
Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	С60Н
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	20 A at 30 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	10 kA lcu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA lcu at 400415 V AC 50/60 Hz conforming to EN/IEC 60947-2 10000 A lcn at 230/400 V AC 50/60 Hz conforming to EN 60898 25 kA lcu at 125 V DC 2P conforming to EN/IEC 60947-2 30 kA lcu at 230240 V AC 50/60 Hz conforming to EN/IEC 60947-2 40 kA lcu at 125 V DC 3P conforming to EN/IEC 60947-2 50 kA lcu at <= 250 V DC 4P conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz 230240 V AC 50/60 Hz 400415 V AC 50/60 Hz <= 250 V DC 230/400 V AC 50/60 Hz
Magnetic Tripping Limit	510 x In
[Ics] Rated Service Breaking Capacity	7.5 kA conforming to EN/IEC 60947-2 - 400415 V AC 50/60 Hz 7500 A conforming to EN 60898 - 230/400 V AC 50/60 Hz 15 kA conforming to EN/IEC 60947-2 - 230240 V AC 50/60 Hz 5 kA conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	73 mm
Net Weight	0.48 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals16 mm² flexible Tunnel type terminals25 mm² rigid
Tightening Torque	Power circuit: 2 N.m upside 2 N.m downside
Earth-Leakage Protection	Separate block
Product Compatibility	C60 auxiliary C60 accessories

Environment

Standards	EN 60898 EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.446 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Certifications & Standards

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
Weee	The product must be disposed on European Union markets following specific waste	
	collection and never end up in rubbish bins	