

# Lembar data produk

Spesifikasi



## die-cast empty control station - XAPM - Ø 22 - zinc alloy - 2 vertical openings

XAPM1202

⚠ Telah dihentikan pada: 20 Okt 2022

⚠ Dihentikan

### Main

|                             |                                                                                                                                               |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Range Of Product            | Harmony XAP                                                                                                                                   |
| Product Or Component Type   | Die-cast empty control station                                                                                                                |
| Device Short Name           | XAPM                                                                                                                                          |
| Product Destination         | For Ø 22 mm control and signalling units                                                                                                      |
| Product Front Plate Size    | 80 x 80 mm                                                                                                                                    |
| Usable Depth                | 49 mm                                                                                                                                         |
| Number Of Cut-Out           | 2 cut-outs                                                                                                                                    |
| Colour Of Base Of Enclosure | Blue                                                                                                                                          |
| Colour Of Cover             | Blue                                                                                                                                          |
| Material                    | Zinc alloy                                                                                                                                    |
| Cable Entry                 | 1 hole with blanking plug for cable gland, clamping capacity: 14 mm<br>1 hole without blanking plug for cable gland, clamping capacity: 14 mm |
| Device Mounting             | Flush                                                                                                                                         |
| Ip Degree Of Protection     | IP65 conforming to IEC 60529<br>IP69 conforming to NF C 20-010<br>IP69K                                                                       |

### Complementary

|                         |         |
|-------------------------|---------|
| Number Of Vertical Rows | 2       |
| Net Weight              | 0.45 kg |

### Environment

|                                       |                                                                      |
|---------------------------------------|----------------------------------------------------------------------|
| Protective Treatment                  | TC                                                                   |
| Ambient Air Temperature For Storage   | -40...70 °C                                                          |
| Ambient Air Temperature For Operation | -40...70 °C                                                          |
| Overvoltage Category                  | Class I conforming to IEC 60536<br>Class I conforming to NF C 20-030 |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 9.5 cm |

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                  |        |
|------------------|--------|
| Package 1 Width  | 9.7 cm |
| Package 1 Length | 10 cm  |
| Package 1 Weight | 514 g  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

Kinerja kesejahteraan

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |


Sertifikasi & Standar

|                          |                                                                                                   |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                 |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>                                                            |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                     |
| Circularity Profile      | No need of specific recycling operations                                                          |

Dimensions Drawings

Dimensions and Fixing

Refer to the product characteristics to get the number of cut-outs.



- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3) 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
- P Usable depth

| a  |      | b  |      | c    |      | G  |      | H  |      | P  |      |
|----|------|----|------|------|------|----|------|----|------|----|------|
| mm | in.  | mm | in.  | mm   | in.  | mm | in.  | mm | in.  | mm | in.  |
| 80 | 3.15 | 80 | 3.15 | 51.5 | 2.01 | 50 | 1.97 | 65 | 2.56 | 49 | 1.93 |