Product datasheet

Specifications





Multi9 - C60 UL489 - MCB - 1P - 6 A - D Curve - 120 V - 10 kA tunnel term

60124

() Discontinued on: 30 Jun 2021

Main

wain		
Range	Multi9	
Product Name	Multi9 C60	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C60 UL489	
Device Application	Distribution	
Poles Description	1P	
Number Of Protected Poles	1	
[In] Rated Current	6 A at 25 °C	
Network Type	AC DC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	D	
Breaking Capacity	5 kA AIR at 240 V AC conforming to UL 489 10 kA Icu at 240 V AC conforming to EN/IEC 60947-2 10 kA Icu at 240 V AC conforming to GB 14048.2 10 kA Icu at 60 V DC conforming to EN/IEC 60947-2 10 kA Icu at 60 V DC conforming to GB 14048.2 10 kA AIR at 120 V AC conforming to UL 489 10 kA AIR at 60 V DC conforming to UL 489 10 kA AIR at 120 V AC conforming to CSA C22.2 No 5.2 5 kA AIR at 240 V AC conforming to CSA C22.2 No 5.2 10 kA AIR at 60 V DC conforming to CSA C22.2 No 5.2	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC
	60 V DC
	120 V AC
Magnetic Tripping Limit	12 x ln +/- 20 % AC
	17 x ln +/- 20 % DC
Limitation Class	3 conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	2	
Height	107 mm	
Width	18 mm	
Depth	73 mm	
Net Weight	0.11 kg	
Colour	Grey	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	
Provision For Padlocking	Padlockable	
Connections - Terminals	Tunnel type terminal (top or bottom)2.525 mm ² (AWG 14AWG 4) - rigid	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	2.5 N.m top or bottom	

Environment

Standards	GB 14048.2 EN/IEC 60947-2 UL 489 CSA C22.2 No 5
Product Certifications	CSA CCC IEC UL
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-3070 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	1.8 cm
Package 1 Length	7.6 cm
Package 1 Weight	130 g

Contractual warranty

Warranty

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins