

Product datasheet

Specifications



2 pole switch with zero setting, iCMB

A9E15120

Main

Range Of Product	Acti9
Product Name	Acti9 iCM
Product Or Component Type	Selector switch
Device Short Name	iCMB
Device Application	Electrical circuit control
Contacts Type And Composition	2 C/O
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
Standards	VDE 0660 part 107 IEC 60947-3 EN 60947-3 UL

Complementary

[Ie] Rated Operational Current	10 A
Maximum Operating Voltage	440 V
Control Type	Rotary handle 3 positions
Marking	1 - 0 - 2
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	60 mm
Width	36 mm
Depth	75 mm
Net Weight	58 g
Colour	White
Mechanical Durability	1000000 cycles
Electrical Durability	AC-21A: 200000 cycles
Connections - Terminals	Jumper terminals1.5 mm²
Wire Stripping Length	9 mm for downside connection
Tightening Torque	1 N.m downside

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
-------------------------	------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	7.6 cm
Package 1 Length	8.4 cm
Package 1 Weight	74.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	80
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.407 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins