
Product datasheet

Specifications





Circuit breaker frame, MasterPact NW63H1, 6300A, 100kA/440VAC 50/60Hz (Icu), 3 poles, fixed, without control unit

48118

Main

Range	MasterPacT	
-		
Product Name	MasterPact NW	
Circuit Breaker Name	MasterPact NW63H1	
Product Or Component Type	Circuit breaker	
Device Application	Power distribution protection	
Poles Description	3P	
Control Unit	Without control unit	
[In] Rated Current	6300 A at 40 °C	
Performance Type	H1 100 kA 440 V AC	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Selectivity Category	Category B	
Control Type	Push-button	
Mounting Mode	Fixed	

Complementary

• •	
[Icu] Rated Ultimate Short-Circuit	100 kA at 220/415 V AC 50/60 Hz
Breaking Capacity	100 kA at 440 V AC 50/60 Hz
	100 kA at 525 V AC 50/60 Hz
	100 kA at 690 V AC 50/60 Hz
[Ics] Rated Service Breaking	100 kA at 220/415 V AC 50/60 Hz
Capacity	100 kA at 440 V AC 50/60 Hz
	100 kA at 525 V AC 50/60 Hz
	100 kA at 690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand	100 kA 1 s
Current	100 kA 3 s
[Icm] Rated Short-Circuit Making	220 kA 220/415 V AC at 50/60 Hz
Capacity	220 kA 440 V AC at 50/60 Hz
	220 kA 525 V AC at 50/60 Hz
	220 kA 690 V AC at 50/60 Hz
Sensor Rating	3200 A
	6300 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	1050 W
Maximum Breaking Time	25 ms

Maximum Closing Response Time	80 ms
Mounting Support	Backplate Rails
Upside Connection	Rear
Downside Connection	Rear
Connection Pitch	230 mm
Mechanical Durability	10000 cycles with maintenance 5000 cycles without maintenance
Electrical Durability	1500 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 1500 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 AC-23A: 1500 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-23A: 1500 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming to EN/ IEC 60947-3
Height	352 mm
Width	767 mm
Depth	297 mm
Net Weight	120 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2
Product Certifications	CE CCC EAC

Environment

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	4 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	75.0 cm
Package 1 Width	75.0 cm
Package 1 Length	120.0 cm
Package 1 Weight	133.41 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information