# **Product datasheet**

Specification





# Circuit breaker, TeSys GB2, 1P, 10A, Icu 1.5kA at 240V, Thermal magnetic, DIN rail mounted

GB2CB16

#### Main

Range	TeSys
Product Name	TeSys GB2
Device Short Name	GB2
Product Or Component Type	Circuit breaker
Device Application	Control
Poles Description	1P
Network Type	AC/DC
Utilisation Category	Category A conforming to IEC 60947-2 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
Network Frequency	50/60 Hz conforming to IEC 60947-2
Breaking Capacity	2 kA Icu at 110 V AC 50/60 Hz conforming to IEC 60947-2 1.5 kA Icu at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 1.5 kA Icu at 24 V DC conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	75 % at 110 V AC 50/60 Hz conforming to IEC 60947-2 75 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	138 A

### Complementary

Mounting Mode	By clips
Mounting Support	Rail Plate
Mounting Position	Horizontal Vertical
Control Type	Toggle
[In] Rated Current	10 A
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz conforming to IEC 60947-2 277 V AC 60 Hz conforming to CSA C22.2 No 235 277 V AC 60 Hz conforming to UL 1077 48 V DC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-2
Power Dissipation Per Pole	2 W
Mechanical Durability	8000 cycles
Electrical Durability	8000 cycles

24 Apr 2024 Life Is On Schneider

Connections - Terminals	Connector 1 cable(s) 0.756 mm²solid without cable end Connector 2 cable(s) 0.754 mm²solid without cable end Connector 1 cable(s) 0.754 mm²flexible with cable end Connector 2 cable(s) 0.752.5 mm²flexible with cable end
Tightening Torque	1.2 N.m on connector
Mechanical Robustness	Shocks: 22 Gn for 20 ms conforming to IEC 60068-2-27 Vibrations: 5 Gn, 5110 Hz conforming to IEC 60068-2-6
Quantity Per Set	Set of 6
9 Mm Pitches	2
Height	74 mm
Width	15 mm
Depth	67 mm

## **Environment**

Standards	EN/IEC 60947-1 EN/IEC 60947-2 CSA C22.2 No 235 UL 1077
Product Certifications	UL CSA
Protective Treatment	TC
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4080 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1
Operating Altitude	3000 m

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	6.800 cm
Package 1 Length	7.300 cm
Package 1 Weight	52.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.500 cm
Package 2 Width	10.000 cm
Package 2 Length	10.000 cm
Package 2 Weight	331.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	72
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm

Package 3 Weight 4.324 kg

## **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations