

Product datasheet

Specifications



Blank plate, Ultimate, 1 gang, pearl nickel

GU8210PN

Main

Range	Ultimate
Accessory / Separate Part Category	Wiring accessory
Aesthetic Name	Flat plate
Product Or Component Type	Blank plate
Colour Tint	Pearl nickel

Complementary

Range Compatibility	Ultimate Ultimate Flat plate blank plate
Device Mounting	Wall mounted
Fixing Mode	By screws
Number Of Gangs	1 gang
Surface Finish	Polished
Material	Steel
Height	88 mm
Width	88 mm
Depth	15 mm
Net Weight	0.098 kg

Environment

Standards	BS 5733
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	9.400 cm
Package 1 Length	9.600 cm
Package 1 Weight	129.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	42.500 cm
Package 2 Length	50.000 cm
Package 2 Weight	13.470 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	235.520 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration