Product datasheet

Specifications





advanced touchscreen panel, Harmony GTO, 320 x 240pixels QVGA, 3.5inch TFT, 64MB

HMIGTO1300

Main

in an i						
Range Of Product	Harmony GTO					
Product Or Component Type	Advanced touchscreen panel					
Display Colour	65536 colours					
Display Size	3.5 inch					
Supply	External source					
Control Button Type	6 operation defined using Vijeo Designer push-button key F1F6					
Operating System	Harmony					
Battery Type	Lithium battery for internal RAM, autonomy: 100 days, charging time = 5 day(s), battery life = 10 year(s)					

Complementary

Complementary						
Terminal Type	Touchscreen display					
Display Type	Backlit colour TFT LCD					
Display Resolution	320 x 240 pixels QVGA					
Touch Sensitive Zone	1024 x 1024					
Touch Panel	Resistive film, 1000000 cycles					
Backlight Lifespan	50000 hours white at 25 °C					
Brightness	16 levels - control by touch panel 16 levels - control by software					
Character Font	Chinese (simplified Chinese) ASCII (European characters) Japanese (ANK, Kanji) Korean Taiwanese (traditional Chinese)					
[Us] Rated Supply Voltage	24 V DC					
Supply Voltage Limits	19.228.8 V					
Inrush Current	30 A					
Maximum Power Consumption In W	5.2 W when power is not supplied to external devices4.2 W when backlight is OFF4.3 W when backlight is dimmed9.6 W					
Local Signalling	Status LED green, steady for offline Status LED green, steady for operating Status LED orange, flashing for software starting up Status LED red, steady for power supply (ON) Status LED clear, faded for power supply (OFF)					
Software Designation	Vijeo Designer configuration software >= V6.1					
Memory Description	Flash EPROM, 64 MB					

Data Backed Up	128 kB internal RAM (SRAM)				
Downloadable Protocols	Schneider Electric Modicon Modbus Schneider Electric Modicon Uni-TE Schneider Electric Modicon Modbus Plus Schneider Electric Modicon FIPWAY Mitsubishi Melsec third party protocols Omron Sysmac third party protocols Rockwell Automation Allen-Bradley third party protocols Siemens Simatic third party protocols				
Integrated Connection Type	COM1 serial link SUB-D 9, interface: RS232C, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 187.5 kbps compatible with Siemens MPI USB 2.0 type A USB 2.0 type mini B				
Product Mounting	Flush mounting				
Fixing Mode	By 4 screw clamps				
Front Material	РРТ				
Enclosure Material	РРТ				
Type Of Cooling	Natural convection				
Width	132 mm				
Height	106 mm				
Depth	42 mm				
Net Weight	0.4 kg				

Environment

Standards	UL 508 IEC 61131-2 IEC 61000-6-2					
Product Certifications	C-Tick cULus CE KCC UKCA UKEX					
Ambient Air Temperature For Operation	050 °C					
Ambient Air Temperature For Storage	-2060 °C					
Relative Humidity	1090 % without condensation					
Operating Altitude	< 2000 m					
Ip Degree Of Protection	IP20 (rear panel) conforming to IEC 60529 IP65 (front panel) conforming to IEC 60529					
Nema Degree Of Protection	NEMA 4X front panel (indoor use)					
Shock Resistance	147 m/s ² 3 chocks in each direction X, Y and Z conforming to IEC 61131-2					
Vibration Resistance	 9.8 m/s² (f = 9150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming to IEC 61131-2 3.5 mm (f = 59 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming to IEC 61131-2 					
Resistance To Electrostatic Discharge	6 kV contact discharge conforming to IEC 61000-4-2 level 3					

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	12.500 cm
Package 1 Width	18.200 cm
Package 1 Length	21.500 cm
Package 1 Weight	707.000 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.670 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins				
Circularity Profile	End of Life Information				

Product datasheet

Dimensions Drawings


Dimensions

External Dimensions



- 1 Front
- 2 Right Side
- 3 Тор


Installation with Installation Fasteners



(5)

- 1 Left Side
- 2 Front
- 3 Right Side
- 4 Top
- 5 Bottom

Dimensions with Cables




- 1 Left Side
- 2 Rear
- 3 Right Side
- 4 Top
- 5 Bottom

Product datasheet

Mounting and Clearance


Mounting


Panel Cut Dimensions




A		В		С		R	
mm	in.	mm	in.	mm	in.	mm	in.
118.5 (+1, -0)	4.67 (+0.04, -0)	92.5 (+1, -0)	3.64 (+0.04, -0)	1.65	0.060.2	3 max.	0.12 max.

Installation Fastener Dimensions










Installation Requirements

Mounting Angle



When installing the panel in a slanted position with an incline more than 30° , the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan,A/C) to ensure the ambient operating temperature is 40° C or less (104 °F or less).

Clearance

