Specifications





# Cam switch body, Harmony K, mutlifixing, plastic, 2 pole, with 0 position, 90°, 12A

K1B1002HL

Discontinued on: 5 Jul 2023

① Discontinued

#### Main

Range Of Product	Harmony K
Product Or Component Type	Cam switch body
Component Name	К1
[Ith] Conventional Free Air Thermal Current	12 A
Sub-Assembly Composition	Contact blocks + fixing plate
Cam Switch Function	Switch
Off Position	With Off position
Poles Description	2P
Switching Positions	Right: 0° - 90°
Mounting Location	Front
Fixing Mode	Multifixing
Bezel Material	Plastic

#### Complementary

Switching Angle	90 °
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1
[Ithe] Conventional Enclosed Thermal Current	10 A
Rated Operational Power In W	10500 W AC-21, 500 - 660 V 3 phases conforming to IEC 947-3 1100 W AC-3, 230 V 3 phases conforming to IEC 947-3 1500 W AC-23A, 230 V 3 phases conforming to IEC 947-3 1500 W AC-3, 400 V 1 phase conforming to IEC 947-3 1500 W AC-3, 400 V 3 phases conforming to IEC 947-3 1500 W AC-3, 500 V 3 phases conforming to IEC 947-3 2200 W AC-3A, 400 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 400 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 800 W AC-21, 230 V 3 phases conforming to IEC 947-3 8300 W AC-21, 400 V 3 phases conforming to IEC 947-3
[le] Rated Operational Current Ac	<ol> <li>1.8 A at 690 V AC-3 3 phases conforming to IEC 947-3</li> <li>2.8 A at 500 V AC-3 3 phases conforming to IEC 947-3</li> <li>2.8 A at 690 V AC-23A 3 phases conforming to IEC 947-3</li> <li>3.3 A at 400 V AC-3 3 phases conforming to IEC 947-3</li> <li>3.8 A at 500 V AC-23A 3 phases conforming to IEC 947-3</li> <li>4.6 A at 230 V AC-3 3 phases conforming to IEC 947-3</li> <li>4.8 A at 400 V AC-23A 3 phases conforming to IEC 947-3</li> <li>5.6 A at 230 V AC-23A 3 phases conforming to IEC 947-3</li> <li>1 A at 500 V AC-23A 3 phases conforming to IEC 947-3</li> <li>1 A at 500 V AC-15 conforming to IEC 947-5-1</li> <li>2 A at 400 V AC-15 conforming to IEC 947-5-1</li> </ol>

Electrical Durability	1000000 cycles AC-15
	1000000 cycles AC-21
	500000 cycles AC-23
	500000 cycles AC-3
Maximum Operating Rate	2.5 cyc/mn AC-21
	2.5 cyc/mn AC-23
	2.5 cyc/mn AC-3
	8.333 cyc/mn AC-15
Short-Circuit Current	10000 A
Short-Circuit Protection	16 A cartridge fuse, type gG
[Uimp] Rated Impulse Withstand	4 kV in isolating function
Voltage	6 kV conforming to IEC 947-1
Contact Operation	Slow-break
Positive Opening	With
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm <sup>2</sup>
	Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm <sup>2</sup>
Mechanical Durability	1000000 cycles
Net Weight	0.121 kg

### Environment

Standards	IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit CENELEC EN 50013
Product Certifications	CSA 240 V 3 hp 3 phases 2 -pole(s) UL 240 V 0.33 hp 1 phase 2 -pole(s) CSA 240 V 1 hp 1 phase UL 240 V 1 hp 3 phases
Protective Treatment	TC
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-4070 °C
Shock Resistance	30 gn conforming to IEC 68-2-27
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)
Overvoltage Category	Class II conforming to IEC 536 Class II conforming to NF C 20-030

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	6.5 cm
Package 1 Length	6.5 cm
Package 1 Weight	121.0 g

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

**Dimensions Drawings** 

#### Body


#### Front Mounting "Multi-Fixing", 2 or 4 Screws



- a 53 mm/2.09 in.
- a1 77 mm/3.03 in.

**Technical Description** 

#### Link Positions (Factory Mounted)



#### Angular Position of Switch



#### Switching Program



#### Convention Used for Switching Program Representation

Contact closed Contact closed in 2 positions and maintained between the 2 positions Sealed assembly for auto-maintain control Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

