



# cam switch - 1 pole - 90° - 20 A - screw mounting

K2B003TLH

! Discontinued on: 1 Jul 2020

! Discontinued

#### Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K2	
[Ith] Conventional Free Air Thermal Current	20 A	
Product Mounting	Front mounting	
Fixing Mode	Multifixing	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 0 - 1 black marking	
Cam Switch Function	OFF-ON switch	
Return	Spring return from 120° to 90°	
Off Position	With Off position	
Poles Description	1P	
Switching Positions	Right: 0° - 90° - 120°	
Ip Degree Of Protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010	

# Complementary

19 Apr 2024

Switching Angle	30 °	
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1	
[Ithe] Conventional Enclosed Thermal Current	16 A	
Electrical Durability	200000 cycles AC-23 200000 cycles AC-3 600000 cycles AC-15 600000 cycles AC-21	
Maximum Operating Rate	2.5 cyc/mn AC-21 2.5 cyc/mn AC-23 2.5 cyc/mn AC-3 8.333 cyc/mn AC-15	
Short-Circuit Current	10000 A	
Short-Circuit Protection	cuit Protection 20 A cartridge fuse, type gG	
[Uimp] Rated Impulse Withstand Voltage	4 kV in isolating function 6 kV conforming to IEC 947-1	

Contact Operation	Slow-break	
Positive Opening	With	
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm <sup>2</sup> Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm <sup>2</sup>	
Mechanical Durability	1000000 cycles	
Cad Overall Width	45 mm	
Cad Overall Height	45 mm	
Cad Overall Depth	77 mm	
Net Weight	0.115 kg	

# **Environment**

Standards	CENELEC EN 50013 EN 60947-3 for power circuit EN 60947-5-1 for control circuit IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit	
Product Certifications	CSA 240 V 1 hp 1 phase CSA 240 V 3 hp 3 phases 2 pole(s) UL 240 V 1 hp 3 phases UL 240 V 0.33 hp 1 phase 2 pole(s)	
Protective Treatment	TC	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Shock Resistance	30 gn conforming to IEC 68-2-27	
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
Electrical Shock Protection Class	Class II conforming to IEC 536 Class II conforming to NF C 20-030	

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	6.5 cm
Package 1 Length	6.5 cm
Package 1 Weight	115 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


# **Product datasheet**

#### K2B003TLH

**Dimensions Drawings** 

#### **Operating Head and Body**

#### Front Mounting "Multi-Fixing"




- a 53 mm/2.09 in.
- e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.

# **Product datasheet**

# K2B003TLH

**Technical Description** 

#### **Link Positions (Factory Mounted)**



#### **Marking**



#### **Angular Position of Switch**



# **Switching Program**



#### **Convention Used for Switching Program Representation**

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

