



Product datasheet

Specifications



MULTIPLE ELBOW 400 A MADE TO MEASURE

KSA400DMBK4CF

 **Discontinued on:** 9 Dec 2022

 **Discontinued**

Main

Range Of Product	Canalis
Product Name	KS
Product Or Component Type	Multiple elbow
Busbar Description	Fire barrier
Device Application	Change direction
[Ie] Rated Operational Current	100 A at 35 °C 160 A at 35 °C 250 A at 35 °C
Ip Degree Of Protection	IP55 conforming to IEC 60529
[Ue] Rated Operational Voltage	230...690 V
Network Frequency	50/60 Hz
Operating Angle	90 °
Direction Change Type	direction 1: edgewise to downward - neutral to up direction 3: flat to right - neutral to left
Colour	White (RAL 9001)
Dimension Type	Made to measure
Length	250...695 mm for side C 250...745 mm for side A

Complementary

Width	147 mm
Net Weight	9.9 kg
Mounting Mode	By screws
Electrical Connection	Lubricated sliding contact
Standards	IEC 61439-1 IEC 61439-6

Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	77.5 cm
Package 1 Width	92 cm
Package 1 Length	77.9 cm
Package 1 Weight	54 kg

Contractual warranty

Warranty	18 months
----------	-----------