# **Product datasheet**

Specifications





# Circuit breaker basic frame, ComPact NSX400S, 100kA at 415VAC 50/60 Hz, 400A, without trip unit, 3 poles

LV432414

(!) Discontinued

() Discontinued on: 15 Jun 2023

#### Main

Range	ComPact
Range Of Product	ComPact NSX400630
Device Short Name	Compact NSX400S
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX400S
Number Of Poles	3P
[In] Rated Current	400 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	100 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	S 100 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

### Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2	
[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 12 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 12 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 125 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2	
Mechanical Durability	15000 cycles conforming to IEC 60947-2	

Electrical Durability	12000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 3000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 6000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 6000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	45 mm
Protection Type	Without protection
Width (W)	140 mm
Height (H)	255 mm
Depth (D)	110 mm

### Environment

Standards	EN/IEC 60947-2 UL 508	
Product Certifications	UL CSA	
Pollution Degree	3 conforming to IEC 60664-1	
Ip Degree Of Protection	IP40 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-5085 °C	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	15.7 cm
Package 1 Length	29.2 cm
Package 1 Weight	4.486 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	36
Package 2 Height	44 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	178 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information