# **Product datasheet**

Specification





# power meter PowerLogic PM5111, modbus, up to 15th Harmonic, 1DO 33 alarms, MID

METSEPM5111

## Main

Range	PowerLogic
Product Name	PowerLogic PM5000
Device Short Name	PM5111
Product Or Component Type	Power meter

## Complementary

Complementary	
Power Quality Analysis	up to the 15th harmonic
Device Application	Power monitoring
Type Of Measurement	Current
	Voltage
	Frequency
	Power factor
	Energy
	Active and reactive power
Supply Voltage	90450 V AC 4565 Hz
	100300 V DC
Network Frequency	50 Hz
	60 Hz
[In] Rated Current	5 A
	1 A
Type Of Network	3P
	1P + N
	3P + N
Maximum Power Consumption In Va	11 VA at 415 V
Ride-Through Time	80 ms 120 V AC typical
	100 ms 230 V AC typical
	100 ms 415 V AC typical
Display Type	Monochrome graphic LCD
Display Resolution	128 x 128 pixels
Sampling Rate	64 samples/cycle
Measurement Current	508500 mA
Analogue Input Type	Voltage (impedance 5 MOhm)
	Current (impedance <= 0.3 mOhm)
Measurement Voltage	35760 V AC 4565 Hz between phases
-	20440 V AC 4565 Hz between phase and neutral
Frequency Measurement Range	4565 Hz
Number Of Inputs	0

Measurement Accuracy	Active energy +/- 0.5 %
	Reactive energy +/- 2 %
	Active power +/- 0.5 %
	Apparent power +/- 0.5 %
	Frequency +/- 0.05 %
	Power factor +/- 0.5
	Current +/- 0.5 %
	Voltage +/- 0.5 %
	Apparent energy +/- 0.5 %
	Reactive power +/- 2 %
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22
Number Of Outputs	1 digital
Communication Port Protocol	Modbus RTU and ASCII at 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires,
	insulation 2500 V
	JBUS
Communication Port Support	RS485
Data Recording	Time stamping
	Min/max of instantaneous values
Connections - Terminals	Voltage circuit: screw terminal block4
	Control circuit: screw terminal block2
	Current transformer: screw terminal block6
	Input/output circuit: screw terminal block6
	RS485 link: screw terminal block4
Mounting Mode	Flush-mounted
Mounting Support	Framework
Standards	IEC 61557-12:2015
	EN 50470-1
	UL 61010-1
	IEC 62053-24
	IEC 60529
	EN 50470-3
	IEC 62053-22:2020
	IEC 62053-23:2020
	IEC 62052-11:2020
	IEC 62052-31:2015
Product Certifications	CE conforming to IEC 61010-1
	CULus conforming to UL 61010-1
	MID conforming to EN 50470-1
	MID conforming to EN 50470-1
Width	96 mm
Depth	72 mm
Height	96 mm
Net Weight	380 g

#### **Environment**

Electromagnetic	Compatibility	Surge in

Surge immunity test class A conforming to IEC 61000-4-5

Voltage dips and interruptions immunity test level 4 conforming to IEC 61000-4-11

Limits for harmonic current emissions class A conforming to IEC 61000-3-2

Electrostatic discharge level 4 conforming to IEC 61000-4-2

Conducted RF disturbances level 3 conforming to IEC 61000-4-6

Magnetic field at power frequency level 4 conforming to IEC 61000-4-8

Conducted and radiated emissions class B conforming to EN 55022

Immunity to conducted disturbances - test level: 150 kHz...80 MHz conforming to IEC

61000-4-6

Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Radiated radio-frequency electromagnetic field immunity test conforming to IEC

Surge immunity test conforming to IEC 61000-4-5

Voltage dips and interruptions immunity test conforming to IEC 61000-4-11

Limitation of voltage changes, voltage fluctuations and flicker in low-voltage

conforming to IEC 61000-3-3

Conducted RF disturbances conforming to IEC 61000-4-6 Immunity to impulse waves conforming to IEC 61000-4-12

Ip Degree Of Protection	IP54 display: conforming to IEC 60529 IP30 rear: conforming to IEC 60529
Relative Humidity	595 % at 50 °C non-condensing
Pollution Degree	2
Ambient Air Temperature For Operation	-2570 °C meter -2070 °C display -2520 °C (with reduced performance) display
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	2000 m CAT III 3000 m CAT II

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	12.5 cm
Package 1 Length	13.0 cm
Package 1 Weight	550.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.64 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	96
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	61.82 kg

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information