Product datasheet

Specifications





power meter PowerLogic PM5331, modbus, up to 31st Harmonic, 256KB 2DI/2DO 35 alarms, MID

METSEPM5331

Main	
Range	PowerLogic
Product Name	PowerLogic PM5000
Device Short Name	PM5331
Product Or Component Type	Power meter

Complementary

Complementary	
Power Quality Analysis	up to the 31st harmonic
Device Application	Power monitoring Multi-tariff
Type Of Measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply Voltage	90450 V AC 4565 Hz 100300 V DC
Network Frequency	50 Hz 60 Hz
[In] Rated Current	1 A 5 A
Type Of Network	1P + N 3P 3P + N
Maximum Power Consumption In Va	11 VA at 415 V
Ride-Through Time	80 ms 120 V AC typical 100 ms 230 V AC typical 100 ms 415 V AC typical 50 ms 125 V DC typical
Display Type	Monochrome graphic LCD
Display Resolution	128 x 128 pixels
Sampling Rate	64 samples/cycle
Measurement Current	58500 mA
Analogue Input Type	Voltage (impedance 5 MOhm) Current (impedance <= 0.3 mOhm)
Measurement Voltage	35760 V AC 4565 Hz between phases 20400 V AC 4565 Hz between phase and neutral
Frequency Measurement Range	4565 Hz
Number Of Inputs	2 digital

Measurement Accuracy	Active energy +/- 0.5 %
-	Reactive energy +/- 2 %
	Active power +/- 0.5 %
	Apparent power +/- 0.5 %
	Frequency +/- 0.05 %
	Power factor +/- 0.5
	Current +/- 0.5 %
	Voltage +/- 0.5 %
	Apparent energy +/- 0.5 %
	Reactive power +/- 2 %
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22
Number Of Outputs	2 relay
	2 digital
Information Displayed	Tariff (4)
Communication Port Protocol	Modbus RTU and ASCII at 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires,
	insulation 2500 V
	JBUS
Communication Port Support	R\$485
Data Recording	Alarm logs
	Min/max of instantaneous values
	Data logs
	Time stamping
	Maintenance logs
	Event logs
Memory Capacity	256 kB
Connections - Terminals	Voltage circuit: screw terminal block4
	Control circuit: screw terminal block2
	Current transformer: screw terminal block6
	Input/output circuit: screw terminal block6
	Relay output: screw terminal block4
	Ethernet network: RJ45 connector
Mounting Mode	Flush-mounted
Mounting Support	Framework
Standards	EN 50470-3
	IEC 62053-22:2020
	IEC 61557-12:2015
	UL 61010-1
	IEC 62053-24
	EN 50470-1
	IEC 60529
	IEC 62053-23:2020
	IEC 62052-11:2020
	IEC 62052-31:2015
Product Certifications	CE conforming to IEC 61010-1
	CULus conforming to UL 61010-1
	MID conforming to EN 50470-1
	MID conforming to EN 50470-3
Width	96 mm
Depth	72 mm
Height	96 mm
Net Weight	430 g
· · · · •	

Environment

Electromagnetic Compatibility	Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 Surge immunity test level 4 conforming to IEC 61000-4-5 Voltage dips and interruptions immunity test level 3 conforming to IEC 61000-4-11 Limits for harmonic current emissions class A conforming to IEC 61000-3-2 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency level 4 conforming to IEC 61000-4-8 Conducted and radiated emissions class B conforming to EN 55022 Limitation of voltage changes, voltage fluctuations and flicker in low-voltage
	conforming to IEC 61000-3-3
	Electrostatic discharge - test level: 8 kV level 4 conforming to IEC 61000-4-2
	Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3
	Voltage dips and interruptions immunity test - test level: 8 kV level 4 conforming to IEC 61000-4-11
Ip Degree Of Protection	IP54 display: conforming to IEC 60529 IP30 rear: conforming to IEC 60529
Relative Humidity	595 % at 50 °C non-condensing
Pollution Degree	2
Ambient Air Temperature For Operation	-2570 °C meter -2070 °C display -2520 °C (with reduced performance) display
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	2000 m CAT III 3000 m CAT II

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	12.5 cm
Package 1 Length	12.7 cm
Package 1 Weight	550.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.92 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information