Product datasheet





servo motor MH3 070 3,1Nm,no key, single 16 lines, brake, IP65/ IP67,6kRPM

MH30703P06F2200

! Discontinued on: 30 Aug 2022

! Discontinued

Main

Range Compatibility	PacDrive 3
Product Or Component Type	AC servo motors
Device Short Name	MH3

Complementary

•	
Maximum Mechanical Speed	8000 rpm
[Us] Rated Supply Voltage	115480 V
Network Number Of Phases	Three phase
Continuous Stall Current	3.91 A
Continuous Stall Torque	3.4 N.m, 115480 V, three phase
Continuous Power	1540 W
Peak Stall Torque	10.2 N.m, 115480 V, three phase
Nominal Output Power	0.42 W, 115 V
	0.75 W, 230 V
	1.32 W, 400 V
	1.54 W, 480 V
Nominal Torque	3.18 N.m for LXM52 at 3.56 mA, 115 V, 1 phase
	2.96 N.m for LXM52 at 3.47 mA, 230 V, 1 phase
	2.53 N.m for LXM52 at 3.02 mA, 400 V, 3 phases
	2.26 N.m for LXM52 at 2.74 mA, 480 V, 3 phases
	3.18 N.m for LXM62 at 3.56 mA, 115 V, 1 phase
	2.96 N.m for LXM62 at 3.47 mA, 230 V, 1 phase
	2.53 N.m for LXM62 at 3.02 mA, 400 V, 3 phases
	2.26 N.m for LXM62 at 2.74 mA, 480 V, 3 phases
Nominal Speed	1250 rpm for LXM52 at 3.56 mA, 115 V, 1 phase
	2500 rpm for LXM52 at 3.47 mA, 230 V, 1 phase
	5000 rpm for LXM52 at 3.02 mA, 400 V, 3 phases
	6500 rpm for LXM52 at 2.74 mA, 480 V, 3 phases
	1250 rpm for LXM62 at 3.56 mA, 115 V, 1 phase
	2500 rpm for LXM62 at 3.47 mA, 230 V, 1 phase
	5000 rpm for LXM62 at 3.02 mA, 400 V, 3 phases
	6500 rpm for LXM62 at 2.74 mA, 480 V, 3 phases
Maximum Current Irms	12.57 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	14 mm
Shaft Length	30 mm
Ip Degree Of Protection	IP65 standard

Encoder Type	Single turn SinCos Hiperface
Speed Feedback Resolution	16 periods
Holding Brake	With
Holding Torque	3 N.m
Mounting Support	International standard flange
Motor Flange Size	70 mm
Electrical Connection	Rotatable right-angled connectors
Torque Constant	0.87 N.m/A at 120 °C
Back Emf Constant	55 V/krpm
Number Of Motor Poles	10
Rotor Inertia	1.78 kg.cm²
Stator Resistance	2.65 Ohm
Stator Inductance	8.64 mH
Stator Electrical Time Constant	3.2 ms
Maximum Radial Force Fr	730 N at 1000 rpm 580 N at 2000 rpm 510 N at 3000 rpm 460 N at 4000 rpm 430 N at 5000 rpm 400 N at 6000 rpm
Brake Pull-In Power	7 W
Type Of Cooling	Natural convection
Length	225 mm
Centring Collar Diameter	60 mm
Centring Collar Depth	2.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.5 mm
Circle Diameter Of The Mounting Holes	82 mm
Net Weight	4 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	19.0 cm
Package 1 Length	39.5 cm
Package 1 Weight	2.5 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration