Product datasheet

Specification





impulse relay iTLI - 2P - 1NO+1NC - 16A - coil 24 VDC - 48 VAC 50/60Hz

A9C30215

Main

Wall		
Range Of Product	Acti9	
Product Name	Acti9 iTL	
Product Or Component Type	Impulse relay	
Device Short Name	iTLi	
Device Application	Changeover relay	
Poles	2P	
Pole Contact Composition	1 NO + 1 NC	
[In] Rated Current	16 A	
Network Type	AC	
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 24 V DC	

Complementary

Network Frequency	50/60 Hz	
	30/00 FIZ	
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz	
Control Type	Coil deconnection	
	Remote and manual control	
Control Signal Type	Impulse	
Switching Frequency	5 switching operations/minute	
	100 switching operations/day	
Impulse Duration	50 ms1 s	
Remote Control Type	Illuminated push-button 3 mA	
Local Signalling	ON/OFF indication	
Mounting Mode	Fixed	
Mounting Support	DIN rail	
9 Mm Pitches	2	
Height	84 mm	
Width	18 mm	
Depth	60 mm	
Electrical Durability	AC-21: 200000 cycles	
	AC-22: 100000 cycles	

Connections - Terminals	Control circuit: tunnel type terminals 1 cable(s) 0.54 mm² rigid Control circuit: tunnel type terminals 1 cable(s) 0.54 mm² rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 14 mm² flexible Control circuit: tunnel type terminals 1 cable(s) 14 mm² flexible with ferrule Power circuit: tunnel type terminals 1 cable(s) 1.54 mm² rigid Power circuit: tunnel type terminals 1 cable(s) 1.54 mm² rigid with cable end Power circuit: tunnel type terminals 1 cable(s) 1.54 mm² flexible Power circuit: tunnel type terminals 1 cable(s) 1.54 mm² flexible with ferrule	
Wire Stripping Length	11 mm	
Tightening Torque	1 N.m	
Range Compatibility	Acti 9 iATEt Acti 9 iATLc Acti 9 iATLc+s Acti 9 iATLm Acti 9 iATLs Acti 9 iETL iTL 16 Acti 9 iATLc+c	

Environment

Standards	EN 669-2-2 EN 669-1	
Product Certifications	CCC GOST	
Quality Labels	KEMA IMQ NF VDE CEBEC	
Noise Level	60 dB	
Ip Degree Of Protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)	
Pollution Degree	3	
Tropicalisation	2	
Relative Humidity	95 % at 55 °C	
Ambient Air Temperature For Operation	For -2050 °C	
Ambient Air Temperature For Storage	-4070 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	111.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	23.0 cm
Package 2 Weight	1.394 kg
Unit Type Of Package 3	S03

Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.304 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations