

Product datasheet

Specifications



Right door S3X 316L 1000x1000mm

NSYDS3X1010RH

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Right door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial S3X
Device Composition	1 door locking system
Quantity Per Set	Set of 1

Complementary

Material	Door: stainless steel 316L
Surface Finish	Scotch-Brite® brushed
Lock Type	3 points lock, 3 mm double-bar
Number Of Locks	1
Door Type	Plain
Door Opening Side	Right (120 °)
Height	1000 mm
Width	500 mm
Net Weight	7.583 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	81.0 cm
Package 1 Length	121.0 cm
Package 1 Weight	7.583 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	6
Package 2 Height	45.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	64.724 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information