Product datasheet

Specification





discrete IO module, Modicon TM3, 24 IO, 16 inputs, 8 relay outputs, spring, 24V DC

TM3DM24RG

Main

Range Of Product	Modicon TM3	
Product Or Component Type	Discrete I/O module	
Range Compatibility	Modicon M241 Modicon M251 Modicon M221 Modicon M262	
Discrete Input Number	16 for input conforming to IEC 61131-2 Type 1	
Discrete Input Logic	Sink or source (positive/negative)	
Discrete Input Voltage	24 V	
Discrete Input Current	7 mA for input	
Discrete Output Type	Relay normally open	
Discrete Output Number	8	
Discrete Output Logic	Positive or negative	
Discrete Output Voltage	24 V DC for relay output 240 V AC for relay output	
Discrete Output Current	2000 mA for relay output	

Complementary

Discrete I/O Number 24		
Current Consumption	5 mA at 5 V DC via bus connector (at state off) 0 mA at 24 V DC via bus connector (at state on) 0 mA at 24 V DC via bus connector (at state off) 65 mA at 5 V DC via bus connector (at state on)	
Discrete Input Voltage Type	DC	
Voltage State 1 Guaranteed	1528.8 V for input	
Current State 1 Guaranteed	>= 2.5 mA (input)	
Voltage State 0 Guaranteed	05 V for input	
Current State 0 Guaranteed	<= 1 mA (input)	
Input Impedance	3.4 kOhm	
Response Time	4 ms (turn-on) 4 ms (turn-off)	
Maximum Current Per Output Common	7 A	
Mechanical Durability	20000000 cycles	
Minimum Load	10 mA at 5 V DC for relay output	
Local Signalling	1 LED per channel (green) for I/O state	

Electrical Connection	17 x 1.5 mm² removable spring terminal block with pitch 3.81 mm adjustment for	
	inputs	
	11 x 1.5 mm² removable spring terminal block with pitch 3.81 mm adjustment for	
	outputs	
Maximum Cable Distance Between Devices	Unshielded cable: <30 m for regular input	
Insulation	Between input and internal logic at 500 V AC	
	Non-insulated between inputs	
	Between input groups and output groups at 1500 V AC	
	Between open contact at 750 V AC	
	Between output and internal logic at 500 V AC	
	Non-insulated between outputs	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715	
	Top hat type TH35-7.5 rail conforming to IEC 60715	
	plate or panel with fixing kit	
Height	90 mm	
Depth	84.6 mm	
Width	42.9 mm	

Environment

Environment	
Standards	IEC 61131-2
Product Certifications	CULus CE UKCA RCM EAC CULus HazLoc
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2
lesistance To Electromagnetic ields 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3	
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	1 kV for I/O conforming to IEC 61000-4-4 2 kV for relay output conforming to IEC 61000-4-4
Surge Withstand	2 kV output common mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Radiated emissions - test level: 40 dB μ V/m QP class A (10 m) at 30230 MHz conforming to IEC 55011 Radiated emissions - test level: 47 dB μ V/m QP class A (10 m) at 2301000 MHz conforming to IEC 55011
Ambient Air Temperature For -1035 °C vertical installation Operation -1055 °C horizontal installation	
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ip Degree Of Protection IP20 with protective cover in place	
Pollution Degree 2	
Operating Altitude	02000 m
Storage Altitude	03000 m

Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail	
	3 gn at 8.4…150 Hz on DIN rail	
	3.5 mm at 58.4 Hz on panel	
	3 gn at 8.4150 Hz on panel	
Shock Resistance	15 an for 11 ms	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	12.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	270.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.787 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	75 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	96 kg

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
Ø	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

19 Apr 2024

TM3DM24RG

Dimensions Drawings

Dimensions




(*) 8.5 mm/0.33 in. when the clamp is pulled out.


Product datasheet

TM3DM24RG


Mounting and Clearance

Spacing Requirements







Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface



(1) Install a mounting strip


Mounting Hole Layout



Connections and Schema


Digital Mixed I/O Module (24-channel)

Wiring Diagram (Source)



- (*) Type T fuse
- (1) The COM0, COM1 and COM2 terminals are not connected internally.
- (2) To improve the life time of the contacts, and to protect from potential inductive load damage, it is recommended to connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.
- (A) Sink wiring (positive logic)
- (C) Source wiring (positive logic)

Wiring Diagram (Sink)



Product datasheet

TM3DM24RG

- (*) Type T fuse
- (1) The COM0, COM1 and COM2 terminals are **not** connected internally.
- (2) To improve the life time of the contacts, and to protect from potential inductive load damage, it is recommended to connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.
- (B) Source wiring (negative logic)
- (D) Sink wiring (negative logic)