

Product datasheet

Specifications



Battery Breaker Kit, 630A, one circuit breaker for Easy UPS 3M/3L

E3MBBK100K200H

Overview

Presentation	Battery breaker kit that controls DC voltage sent from third party battery solutions to the UPS.
Lead Time	Usually Ships within 6 Weeks

Main

Battery Type	VRLA
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cabinet
Battery Power In Vah	0 VAh

Physical

Height	53 cm
Width	32 cm
Depth	23 cm
Net Weight	13 kg
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...4921 ft
Relative Humidity	0...95 % non-condensing

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	80 cm
Package 1 Width	57 cm
Package 1 Length	50 cm
Package 1 Weight	29 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant with Exemptions
China Rohs Regulation		China RoHS declaration Product out of China RoHS scope. Substance declaration for your information