Product datasheet





Link 150 - ethernet gateway - 2 Ethernetport - 24 V DC and PoE

EGX150

Main

Range	Enerlin'X	
Product Name	Link	
Product Or Component Type	Gateway	
Device Short Name	Link150	
Device Application	Gateway	
External Supply	External supply: 19.226.4 V DC, <500 mA	
Poe	Power supply device PoE conforming to IEEE 802.3af	
Number Of Port	2	
Communication Gateway	Ethernet/fieldbus	

Complementary

Current Consumption	130 mA at 24 V DC via external supply (20 °C) 65 mA at 48 V DC via PoE (20 °C)
Maximum Power Consumption In W	15 W via PoE
Communication Network Type	Ethernet, Ethernet Modbus TCP/IP daisy chain even/odd or none parity, at 10/100 Mbit/s Ethernet, PoE 15W (Power over Ethernet) even/odd or none parity, at 10/100 Mbit/s Ethernet, FTP even/odd or none parity, at 10/100 Mbit/s Ethernet, HTTP even/odd or none parity, at 10/100 Mbit/s Ethernet, SNMP even/odd or none parity, at 10/100 Mbit/s Ethernet, Modbus TCP/IP even/odd or none parity, at 10/100 Mbit/s Ethernet, Modbus RTU, JBUS, PowerLogic (SY/MAX) even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS232, Modbus ASCII even/odd or none parity, at 2400, 4800, 9600, 19200, 38400, 56000 or 57600 bauds RS232, Modbus Serial line slave even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus RTU, JBUS, PowerLogic (SY/MAX) even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus ASCII even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus ASCII even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus Serial line slave even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds
	19200 or 38400 bauds
Parity	Even/odd or none
Communication Port Protocol	Ethernet Modbus TCP/IP daisy chain, insulation 6 kV Modbus TCP/IP, insulation 6 kV Modbus RTU, JBUS, PowerLogic (SY/MAX), master - 2 or 4 wires, insulation 2.5 kV Modbus ASCII, master - 2 or 4 wires, insulation 2.5 kV Modbus RTU and ASCII, slave - 2 or 4 wires, insulation 2.5 kV
Communication Port Support	RJ45: ETHERNET RJ45: RS232 RJ45: RS485
Number Of Inputs	0

Life Is On Schneider 25 Apr 2024

Number Of Outputs	0
Connections - Terminals	Power supply: screw terminal block (top) 0.21.5 mm² cable(s) rigid Power supply: screw terminal block (top) 0.21.5 mm² cable(s) flexible with cable end Power supply: screw terminal block (top) 0.21.5 mm² cable(s) flexible without cable
	end
Tightening Torque	Power supply: 0.3 N.m flat screwdriver 3 mm
Wire Stripping Length	Power supply: 7 mm for top connector connection
Mounting Mode	Clip-on
Mounting Support	35 mm DIN rail
Product Certifications	cULus FCC Class A CE RCM UL cUL
Standards	IEC 60950-1 UL 61010-2-201 UL 61010-1 CSA C22.2 No 60950-1 AS/NZS 60950-1 UL 60950-1 IEC 61000-6-2
Depth	72 mm
Height	105 mm
Width	71 mm
Net Weight	175 g
Web Services	Web server
Local Signalling	LED: for Ethernet activity (ETH1) LED: for Ethernet activity (ETH2) LED: for module status LED: for network communication status (Net Status) LED: for communication (RS232) LED: for communication (RS485)
Compatibility Code	EGX150
Environment	

Relative Humidity	595 % at 55 °C without condensation
Ip Degree Of Protection	IP40 (front panel (in enclosure)) IP30 (casing) IP20 (terminal block)
Mechanical Robustness	Vibrations in operation: 1 Gn, 5 Hz150 Hz conforming to IEC 60068-2-6 Vibrations de-energized: 1 Gn, 5 Hz150 Hz conforming to IEC 60068-2-6 Shocks in operation: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks de-energized: 15 Gn for 11 ms conforming to IEC 60068-2-27 Jolts de-energized: 100 jolts/axle, 15 Gn for 6 ms conforming to IEC 60068-2-29 Free fall resistance: 1.2 m

Electromagnetic Compatibility	Immunity for industrial environments conforming to EN 61000-6-2		
	Immunity for industrial environments conforming to CISPR 24		
	Conducted and radiated emissions conforming to FCC part 15 class B		
	Conducted and radiated emissions conforming to EN 55022		
	Conducted and radiated emissions conforming to CISPR 22		
	Electrostatic discharge - test level: 8 kV air, 6 kV contact B conforming to EN 61000-4-2 Radiated RF fields - test level: 10 V/m, 80 MHz1 GHz A conforming to EN 61000-4-3		
			Radiated RF fields - test level: 3 V/m, 1 MHz3 GHz A conforming to EN 61000-4-3 Fast transients immunity test level 4 conforming to EN 61000-4-4
	Fast transient bursts class 3 conforming to EN 61000-4-12		
	Surges - test level: level 4 B (1.2/50 µs) conforming to EN 61000-4-5 Conducted RF disturbances - test level: 10 V conforming to EN 61000-4-6 Conducted RF disturbances conforming to CISPR 11		
		Magnetic field at power frequency - test level: 30 A/m class 5 conforming to EN 61000-4-8	
		Voltage dips and interruptions immunity test - test level: 100 %, 20 ms B conforming to FN 61000-4-11	
	Voltage dips and interruptions immunity test - test level: 60 %, 200 ms B conforming to EN 61000-4-11		
	Voltage dips and interruptions immunity test - test level: 30 $\%$, 500 ms conforming to EN 61000-4-11		
	Ambient Air Temperature For Operation	-2570 °C	
	Ambient Air Temperature For Storage	-4085 °C	
	Pollution Degree	2	

Packing Units

r acking office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	9 cm
Package 1 Length	12.5 cm
Package 1 Weight	304 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.87 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	72 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

25 Apr 2024